



Wesco Industrial Products, Inc.

1250 Welsh Rd

North Wales, PA 19454

**Phone:** 800.445.5681 • **Fax:** 800.346.5511

**Email:** [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 261054, 3" X 42" FORK / 35" - 50" I.D. ADJUSTABLE BASE POWERED STA



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Meets ANSI B56.10 specifications.
- Battery and charger included.
- Forks lower to floor on all models.
- Adjustable base legs.
- Reinforced frame and adjustable base.
- Double chain, lift support.
- Heavy-duty pump.
- Ergonomic "D" handles.
- 5th wheel and power drive options available.
- 110 V AC models available. (special order no cancellations or returns).
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261054

110V AC Powered #261054AC

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#)

### Video



## Specifications

|                              |                      |
|------------------------------|----------------------|
| PART NUMBER                  | 261054               |
| MODEL                        | PASFL-76-42-3550S-2K |
| LIFT HEIGHT                  | 76"                  |
| CAPACITY                     | 2000 lb              |
| WIDTH FORKS                  | 3"                   |
| LENGTH FORKS                 | 42"                  |
| LOAD CENTER                  | 24"                  |
| ADJUSTABLE BASE LEG          | 35" to 50" ID        |
| OVERALL HEIGHT               | 94"                  |
| WEIGHT                       | 657 lb               |
| ADJUSTABLE FORK MIN / MAX OD | 6" / 29"             |

MADE IN THE USA



## 5th Wheel Steering Option

5TH WHEEL STEERING OPTION



5th Wheel Steering Option for easier mobility & precision steering in confined areas. Available only on 1,500 and 2,000 lb models. 8" locking polyurethane wheels. Spring loaded handle. Can be field installed. Order as separate option under Part # 261099

5th wheel steering option