



Wesco Industrial Products, Inc.

1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 261068, 3" X 42" FORK / 35" - 50" I.D. ADJUSTABLE BASE POWERED STA



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Meets ANSI B56.10 specifications.
- Battery and charger included.
- Forks lower to floor on all models.
- Adjustable base legs.
- Reinforced frame and adjustable base.
- Double chain, lift support.
- Heavy-duty pump.
- Ergonomic "D" handles.
- 5th wheel and power drive options available.
- 110 V AC models available. (special order no cancellations or returns).
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261068

110V AC Powered #261068AC

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#)

Video



Specifications

PART NUMBER	261068
MODEL	PASFL-64-42-3550S-1.5K
LIFT HEIGHT	64"
CAPACITY	1500 lb
WIDTH FORKS	3"
LENGTH FORKS	42"
LOAD CENTER	24"
ADJUSTABLE BASE LEG	35" to 50" ID
OVERALL HEIGHT	83"
WEIGHT	587 lb
ADJUSTABLE FORK MIN / MAX OD	6" / 29"

MADE IN THE USA



5th Wheel Steering Option

5TH WHEEL STEERING OPTION



5th Wheel Steering Option for easier mobility & precision steering in confined areas. Available only on 1,500 and 2,000 lb models. 8" locking polyurethane wheels. Spring loaded handle. Can be field installed. Order as separate option under Part # 261099

5th wheel steering option