



Wesco Industrial Products, Inc.

1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 261094, 3" X 25" FORK / 26" O.D. FIXED BASE POWERED STACKER



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Meets ANSI B56.10 specifications.
- Battery and charger included.
- Forks lower to floor on all models.
- Reinforced frame and fixed base.
- Double chain, lift support.
- Heavy-duty pump.
- Ergonomic "D" handles.
- 5th wheel and power drive options available.
- 110V AC models available (Special order no cancellations or returns).
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261094

110V AC Powered #261094AC

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#)

Video



Specifications

PART NUMBER	261094
MODEL	PSFL-76-25-20S-2K
LIFT HEIGHT	76"
CAPACITY	2000 lb
WIDTH FORKS	3"
LENGTH FORKS	25"
LOAD CENTER	15"
BASE LEG (ID/OD)	20"/26"
OVERALL HEIGHT	94"
WEIGHT	611 lb
ADJUSTABLE FORK MIN / MAX OD	6" / 24.5"

MADE IN THE USA



5th Wheel Steering Option

5TH WHEEL STEERING OPTION



5th Wheel Steering Option for easier mobility & precision steering in confined areas. Available only on 1,500 and 2,000 lb models. 8" locking polyurethane wheels. Spring loader handle. Can be field installed. Order as separate option under Part # 261099

5th wheel steering option