



Wesco Industrial Products, Inc.

1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • **Fax:** 800.346.5511

Email: info@wescomfg.com

PART NO. 261105, POWERED LIFT TABLE 32" X 48", 4000 LB CAPACITY, 59" LIFT HEIGHT



- **1-year warranty.**
- Standard floor lock holds table steady for loading and unloading.
- Easy to read illuminated battery status voltmeter.
- With a minimally charged battery, unit can be used while recharging.
- Push-pull, roller and ball tops available on Wesco® 32" x 48" manual and power tables.

[Video](#) | [Specifications](#)

Video



Specifications



PART NUMBER	261105
MODEL	PLT-40-3248
CAPACITY	4000 lb
CASTER	6" Phenolic Resin Wheel (2) Swivel (2) Rigid
TABLE WIDTH	32"
TABLE LENGTH	48"
RAISED HEIGHT	59"
LOWERED HEIGHT	37"
OVERALL WIDTH	32"
OVERALL HEIGHT	37"
OVERALL DEPTH	51.25"
WEIGHT	607 lb
MADE IN THE USA	