



REPLACEMENT PARTS LIST

KIT	ITEM	PART NO.	DESCRIPTION	QTY.
A		170651	KIT: TIGHTENER	
	1		RUBBER BUSH	1
	2		PAWL	1
	3		RETAINING RING	1
	4		BOLT	1
	5		SPRING	1
	6		DENTATION CLIP	1
	7		PIN	1
B		170652	KIT: MOBILE HOOP	
	8		MOBILE HOOP	1
	9		SPRING	1
	10		BOLT	1
	11		LOCKNUT	2
	12		WASHER	1
	13		PIN	1
	14		ELASTIC PIN	1
	15		SUPPORT HOOP	1
	16		CHAIN	1
	17		NUT	1
C		170660	KIT: GEAR WHEEL	
	18		PIN	1
	19		GEAR WHEEL	1
	20		SCREW	1
	21		SEPARATE RING	1
	22		BOLT	1

REPLACEMENT PARTS LIST

KIT	ITEM	PART NO.	DESCRIPTION	QTY.
	23		NOT OFFER	
D		170663	KIT: CHASSIS HARDWARE	
	24		BUSH	1
	25		RETAINING RING	1
	26		BRACE SCREW	2
	27		RETAINING RING	1
	28		BUSH	2
	29		LOCATION FRAME	1
	40		BOLT	1
	41		BRACE BOLT	1
	42		CHAIN	1
E		170659	KIT: CHAIN WHEEL	
	30		WHEEL FOR CHAIN	1
	33		ELASTIC PIN	1
	34		SEPARATE RING	1
F		170661	KIT: PINION	
	35		CHAIN WHEEL	1
	37		SHAFT	1
	38		PIN	1
	39		GEAR SHAFT	1
	16		CHAIN	1
	31	170653	COVER	1
	32	170657	CHAIN	1
	36	170682	CHAIN	1

## Value Fork Drum Lifter & Tilter

- Economically priced lower capacity model.
- Two models, 700 & 1400 lbs. capacities.
- Operator does not have to leave seat to tilt drum.
- Made in China

P/N 272402

Model VFDLT-700  
 Capacity: 440 Half Drum  
 700 Full Drum  
 Fork Pocket Dim.: 7" W x 2.5" H  
 Weight: 154 lbs.  
 Boxed: Yes

THIS DRAWING IN ALL PARTICULARS IS WESCO MFG. CO. PROPERTY. ALL RIGHTS OF DESIGN, INVENTION OR USE OF ARE RESERVED.

01-09-13 UPDATED	R W S	WESCO MANUFACTURING CO. NORTH WALES PENNA. 19454		
	REV. ECH & DATE	REV. S	PART NAME VFDLT-700	DRAWN: RDS 03-15-06
		REV. B	CHECKED:	
	TOLERANCE UNLESS OTHERWISE SPECIFIED		APP. ENGR.	
FRACTION 3 PLACE DECIMAL 2 PLACE DECIMAL		SCALE: 3/16" = 1"		
± 1/64 ± .005 ± .01		C- 272402		
ANGULAR ± 1-1/2°		SHEET 1 OF 1	REV B	
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS				