

Enclosure Subpanels



Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

- 14-gauge
- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized panels have a conductive finish (no paint)
- Panels listed fit the following enclosures:
 - NEMA 1 small (N1C)
 - NEMA 3R small (RHC)
 - NEMA 12 WA_GIE




Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures							
Painted Steel	Price	Galvanized	Price	Perforated	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
N1P0606	\$5.00	N1P0606G	\$5.00	N1P0606PP	\$6.50	6 x 6	4.25 x 4.25 [108 x 108]
N1P0608	\$5.75	N1P0608G	\$5.75	N1P0608PP	\$6.75	6 x 8	6.25 x 4.25 [159 x 108]
N1P0808	\$6.75	N1P0808G	\$6.75	N1P0808PP	\$8.00	8 x 8	6.25 x 6.25 [159 x 159]
N1P0810	\$8.00	N1P0810G	\$8.00	N1P0810PP	\$9.25	8 x 10	8.25 x 6.25 [210 x 159]
N1P1010	\$9.50	N1P1010G	\$9.50	N1P1010PP	\$10.75	10 x 10	8.25 x 8.25 [210 x 210]
N1P1012	\$11.00	N1P1012G	\$11.00	N1P1012PP	\$12.75	10 x 12	10.25 x 8.25 [260 x 210]
N1P1212	\$13.25	N1P1212G	\$13.25	N1P1212PP	\$15.00	12 x 12	10.25 x 10.25 [260 x 260]
N1P1214	\$14.75	N1P1214G	\$14.75	N1P1214PP	\$17.00	12 x 14	12.25 x 10.25 [311 x 260]
N1P1216	\$16.50	N1P1216G	\$16.50	N1P1216PP	\$19.75	12 x 16	14.25 x 10.25 [362 x 260]
N1P1220	\$23.00	N1P1220G	\$23.00	N1P1220PP	\$26.00	12 x 20	18.25 x 10.25 [464 x 260]

Notes: Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawing.

Dimensions



Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25in [6 mm] spacing.