

# Enclosure Subpanels



## Subpanels for Medium NEMA 1 Enclosures

- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Panels listed fit NEMA 1 large (N1C) enclosures
- 14 gauge carbon steel
- Perforated panels have 0.13in [3 mm] diameter holes at 0.25in [6 mm] spacing



### Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.

### Subpanels for Medium NEMA 1 Enclosures

<i>Painted Steel</i>	<i>Price</i>	<i>Perforated</i>	<i>Price</i>	<i>Steel Gauge</i>	<i>Subpanel Size AxB</i>	<i>Drawing Link</i>
<a href="#"><u><b>N1P1216L</b></u></a>	\$17.25	<a href="#"><u><b>N1P1216LPP</b></u></a>	\$19.75	14	13.00 x 10.50 [330 x 267]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P1616</b></u></a>	\$21.00	<a href="#"><u><b>N1P1616PP</b></u></a>	\$26.50	14	13.00 x 14.50 [330 x 368]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P1620</b></u></a>	\$25.00	<a href="#"><u><b>N1P1620PP</b></u></a>	\$29.00	14	17.00 x 14.50 [432 x 368]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P1624</b></u></a>	\$31.00	<a href="#"><u><b>N1P1624PP</b></u></a>	\$35.50	14	21.00 x 14.50 [533 x 368]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2016</b></u></a>	\$25.50	<a href="#"><u><b>N1P2016PP</b></u></a>	\$29.50	14	13.00 x 18.50 [330 x 470]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2020</b></u></a>	\$34.00	<a href="#"><u><b>N1P2020PP</b></u></a>	\$39.00	14	17.00 x 18.50 [432 x 470]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2024</b></u></a>	\$38.50	<a href="#"><u><b>N1P2024PP</b></u></a>	\$44.00	14	21.00 x 18.50 [533 x 470]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2030</b></u></a>	\$83.00	<a href="#"><u><b>N1P2030PP</b></u></a>	\$95.00	14	26.00 x 18.50 [660 x 470]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2420</b></u></a>	\$39.00	<a href="#"><u><b>N1P2420PP</b></u></a>	\$45.00	14	17.00 x 22.50 [432 x 572]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2424</b></u></a>	\$72.00	<a href="#"><u><b>N1P2424PP</b></u></a>	\$83.00	14	21.00 x 22.50 [533 x 572]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2430</b></u></a>	\$96.00	<a href="#"><u><b>N1P2430PP</b></u></a>	\$110.00	14	26.00 x 22.50 [660 x 572]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P2436</b></u></a>	\$98.00	<a href="#"><u><b>N1P2436PP</b></u></a>	\$113.00	14	32.00 x 22.50 [813 x 572]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P3030</b></u></a>	\$116.00	<a href="#"><u><b>N1P3030PP</b></u></a>	\$133.00	14	26.00 x 28.50 [660 x 724]	<a href="#"><u>PDF</u></a>
<a href="#"><u><b>N1P3036</b></u></a>	\$141.00	<a href="#"><u><b>N1P3036PP</b></u></a>	\$162.00	14	32.00 x 28.50 [813 x 724]	<a href="#"><u>PDF</u></a>

Note: Dimensions in inches [millimeters].