

22mm Pushbutton NEMA 12 and 13 Wall-Mount



PBGX9

Applications

Designed to hold all standard 22mm [0.87 in] brands of miniature oil-tight pushbuttons, switches and pilot lights. Provide protection from dirt, dust, oil and water.

Construction

- Fabricated from 14-gauge steel,
- Closed-cell oil-resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" miniature pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 6 or more holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- Grounding provisions provided

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

22mm Pushbutton NEMA 12 and 13 Wall-Mount


Carbon Steel	Price	# Holes	Size HxWxD	Drawing Link
PBGX1	\$81.00	1	3.56 x 3.06 x 3.83 [90 x 78 x 97]	PDF
PBGX2	\$84.00	2	5.44 x 3.06 x 3.83 [138 x 78 x 97]	PDF
PBGX3	\$101.00	3	7.31 x 3.06 x 3.83 [186 x 78 x 97]	PDF
PBGX4	\$111.00	4	9.19 x 3.06 x 3.83 [233 x 78 x 97]	PDF
PBGX6	\$141.00	6	8.81 x 5.31 x 4.58 [224 x 135 x 116]	PDF
PBGX9	\$189.00	9	8.81 x 6.81 x 4.58 [224 x 173 x 116]	PDF
PBGX12	\$175.00	12	10.69 x 6.81 x 4.58 [272 x 173 x 116]	PDF
PBGX20	\$193.00	20	12.56 x 8.31 x 4.58 [319 x 211 x 116]	PDF
PBGX25	\$209.00	25	12.56 x 9.81 x 4.58 [319 x 249 x 116]	PDF

Note: Dimensions in inches [millimeters].

22mm Pushbutton NEMA 12 and 13 Wall-Mount



Dimensions



STANDARD 4-WAY
PUSHBUTTON

PBGX HOLE ARRANGEMENTS

