

**ARCHITECTURAL & ENGINEERING SPECIFICATION**

Exposed, quiet diaphragm-type, chrome plated flushometer valve with a polished exterior. Complete with chloramine resistant, dual seal diaphragm with a clog resistant, triple filtered by-pass. The valve incorporates a 6VDC motor actuator, a battery powered automatic sensor, chrome plated metal cover with manual override push button and 10 degree angled sensor.

**PRODUCT FEATURES**

- Control Stop has internal siphon-guard protection, sweat solder kit, wall flange with set screw.
- High back pressure Vacuum Breaker with one piece hex coupling nut
- Chloramine resistant Internal seals
- Clog resistant, triple filtered by pass
- Adjustable tailpiece
- Spud coupling and flange for top spud connection
- True mechanical override button

**COMPLIANCE AND CERTIFICATION:**

- ADA Compliant
- WaterSense Compliant



This product should be used with a WaterSense labeled counterpart with a compatible flow volume to ensure that the entire system meets the requirements for water efficiency and performance.



**FLOW OPTIONS**

	FLUSH VOLUME GPF	WATERSENSE COMPLIANT
<b>-ONE</b>	1.1	☑
<b>-HET</b>	1.28	☑
<b>-WS1</b>	1.6	
<b>-STANDARD</b>	3.5	

**VALVE HEIGHT OPTIONS**

	DIMENSION A INCH [MM]	DIMENSION B INCH [MM]
<b>-STANDARD</b>	11 1/2" [292]	9 7/8" [251]
<b>-1</b>	16" [406]	14 3/8" [365]
<b>-2</b>	24" [610]	22 3/8" [568]
<b>-3</b>	27" [686]	25 3/8" [645]

**SUFFIX OPTIONS**

- YJ Split Ring Pipe Support
- YK Solid Ring Pipe Support

ARCHITECTURAL & ENGINEERING APPROVAL

The information contained in this document is subject to change without notice. Please contact Zurn for most up to date information.

**Rough-in/Overview dimensions:**

