

# DTX Series Junction Boxes

## Dust-Ignitionproof, Watertight

Cast iron box and cover for surface mounting. Cast aluminum box and cover for surface mounting.

### NEC:

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 9EFG

### Applications

- DTX dust tight and watertight boxes are specially designed and constructed for hazardous locations where ignitable dusts, fibers or flyings are present such as:
- Grain elevators
- Grain storage areas
- Paper mills
- Coal storage facilities
- Textile factories

### Features

- Provided with mounting lugs.
- Mechanically attached gaskets.

### Standard Materials

- Bodies and covers: cast iron
- Gasket: vellumoid
- Cover bolts: stainless steel

### Standard Finishes

- Cast iron bodies and covers: hot dip galvanized finish

### Optional Materials

- Cast aluminum box and cover. Add suffix - **A**.
- For factory installed mounting plate, add suffix - **WYM**
- Refer to *Junction Box Mounting Plate Information* for complete listing of available mounting plates.

### NEC Certifications and Compliances

- UL Standard: UL 886 (UL 1203)
- UL Listed: E10444



# DTX Series Junction Boxes

## Dust-Ignitionproof, Watertight

Cast iron box and cover for surface mounting. Cast aluminum box and cover for surface mounting.

NEC:  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
NEMA 4, 9EFG

ENCLOSURES AND JUNCTION BOXES: NEC/CEC WEATHERPROOF/DUSTPROOF JUNCTION AND OUTLET BOXES

Approximate Thickness Side Walls mm (in)	Maximum Conduit Size (In.-NPT)	Inside Dim. in Millimeters (Inches)					Iron Weight kg (lb)	Aluminum Weight kg (lb)	Catalog Number ①
		L	x	W	x	D			
6.4 (0.25)	3/4	101.6 (4.00)	x	101.6 (4.00)	x	76.2 (3.00)	3.2 (7.00)	0.9 (2.00)	DTX-040403
6.4 (0.25)	3/4	101.6 (4.00)	x	101.6 (4.00)	x	101.6 (4.00)	3.6 (8.00)	1.4 (3.00)	DTX-040404
6.4 (0.25)	3/4	127.0 (5.00)	x	127.0 (5.00)	x	101.6 (4.00)	3.6 (8.00)	1.4 (3.00)	DTX-050504
6.4 (0.25)	3/4	152.4 (6.00)	x	101.6 (4.00)	x	76.2 (3.00)	3.6 (8.00)	1.4 (3.00)	DTX-060403
6.4 (0.25)	3/4	152.4 (6.00)	x	101.6 (4.00)	x	101.6 (4.00)	3.6 (8.00)	1.4 (3.00)	DTX-060404
6.4 (0.25)	3/4	152.4 (6.00)	x	152.4 (6.00)	x	76.2 (3.00)	5.0 (11.00)	1.8 (4.00)	DTX-060603
6.4 (0.25)	3/4	152.4 (6.00)	x	152.4 (6.00)	x	101.6 (4.00)	6.8 (15.00)	2.7 (6.00)	DTX-060604
6.4 (0.25)	3/4	152.4 (6.00)	x	152.4 (6.00)	x	152.4 (6.00)	8.2 (18.00)	3.2 (7.00)	DTX-060606
6.4 (0.25)	3/4	203.2 (8.00)	x	101.6 (4.00)	x	76.2 (3.00)	5.0 (11.00)	1.8 (4.00)	DTX-080403
6.4 (0.25)	3/4	203.2 (8.00)	x	101.6 (4.00)	x	101.6 (4.00)	5.4 (12.00)	2.3 (5.00)	DTX-080404
6.4 (0.25)	3/4	203.2 (8.00)	x	152.4 (6.00)	x	76.2 (3.00)	6.8 (15.00)	2.7 (6.00)	DTX-080603
6.4 (0.25)	3/4	203.2 (8.00)	x	152.4 (6.00)	x	101.6 (4.00)	7.3 (16.00)	2.7 (6.00)	DTX-080604
6.4 (0.25)	3/4	203.2 (8.00)	x	152.4 (6.00)	x	152.4 (6.00)	10.00 (22.00)	3.6 (8.00)	DTX-080606
6.4 (0.25)	3/4	203.2 (8.00)	x	203.2 (8.00)	x	101.6 (4.00)	10.9 (24.00)	4.1 (9.00)	DTX-080804
6.4 (0.25)	3/4	203.2 (8.00)	x	203.2 (8.00)	x	152.4 (6.00)	13.2 (29.00)	5.0 (11.00)	DTX-080806
6.4 (0.25)	3/4	203.2 (8.00)	x	203.2 (8.00)	x	203.2 (8.00)	15.0 (33.00)	5.9 (13.00)	DTX-080808
6.4 (0.25)	3/4	254.0 (10.00)	x	152.4 (6.00)	x	101.6 (4.00)	10.00 (22.00)	3.6 (8.00)	DTX-100604
6.4 (0.25)	3/4	254.0 (10.00)	x	152.4 (6.00)	x	152.4 (6.00)	10.9 (24.00)	4.1 (9.00)	DTX-100606
6.4 (0.25)	3/4	254.0 (10.00)	x	203.2 (8.00)	x	101.6 (4.00)	13.2 (29.00)	5.0 (11.00)	DTX-100804
6.4 (0.25)	3/4	254.0 (10.00)	x	203.2 (8.00)	x	152.4 (6.00)	15.4 (34.00)	5.9 (13.00)	DTX-100806
6.4 (0.25)	3/4	254.0 (10.00)	x	203.2 (8.00)	x	203.2 (8.00)	18.6 (41.00)	6.8 (15.00)	DTX-100808
6.4 (0.25)	3/4	254.0 (10.00)	x	254.0 (10.00)	x	101.6 (4.00)	14.1 (31.00)	5.4 (12.00)	DTX-101004
6.4 (0.25)	3/4	254.0 (10.00)	x	254.0 (10.00)	x	152.4 (6.00)	17.7 (39.00)	6.8 (15.00)	DTX-101006
6.4 (0.25)	3/4	254.0 (10.00)	x	254.0 (10.00)	x	203.2 (8.00)	20.4 (45.00)	8.2 (18.00)	DTX-101008
6.4 (0.25)	3/4	304.8 (12.00)	x	101.6 (4.00)	x	101.6 (4.00)	10.4 (23.00)	4.1 (9.00)	DTX-120404
6.4 (0.25)	3/4	304.8 (12.00)	x	152.4 (6.00)	x	101.6 (4.00)	12.2 (27.00)	4.5 (10.00)	DTX-120604
6.4 (0.25)	3/4	304.8 (12.00)	x	152.4 (6.00)	x	152.4 (6.00)	14.5 (32.00)	5.4 (12.00)	DTX-120606
6.4 (0.25)	3/4	304.8 (12.00)	x	203.2 (8.00)	x	101.6 (4.00)	14.1 (31.00)	5.4 (12.00)	DTX-120804
6.4 (0.25)	3/4	304.8 (12.00)	x	203.2 (8.00)	x	152.4 (6.00)	18.1 (40.00)	6.8 (15.00)	DTX-120806
6.4 (0.25)	3/4	304.8 (12.00)	x	203.2 (8.00)	x	203.2 (8.00)	21.8 (48.00)	8.2 (18.00)	DTX-120808
6.4 (0.25)	3/4	304.8 (12.00)	x	254.0 (10.00)	x	101.6 (4.00)	20.0 (44.00)	7.7 (17.00)	DTX-121004
6.4 (0.25)	3/4	304.8 (12.00)	x	254.0 (10.00)	x	152.4 (6.00)	21.3 (47.00)	8.2 (18.00)	DTX-121006
6.4 (0.25)	3/4	304.8 (12.00)	x	254.0 (10.00)	x	203.2 (8.00)	22.7 (50.00)	8.6 (19.00)	DTX-121008
6.4 (0.25)	3/4	304.8 (12.00)	x	304.8 (12.00)	x	101.6 (4.00)	20.4 (45.00)	7.7 (17.00)	DTX-121204
6.4 (0.25)	3/4	304.8 (12.00)	x	304.8 (12.00)	x	152.4 (6.00)	24.5 (54.00)	8.6 (19.00)	DTX-121206
7.9 (0.31)	2	304.8 (12.00)	x	304.8 (12.00)	x	177.8 (7.00)	27.2 (60.00)	10.0 (22.00)	DTX-121207
7.9 (0.31)	2	304.8 (12.00)	x	304.8 (12.00)	x	203.2 (8.00)	29.9 (66.00)	11.3 (25.00)	DTX-121208
7.9 (0.31)	2	304.8 (12.00)	x	304.8 (12.00)	x	254.0 (10.00)	32.7 (72.00)	12.2 (27.00)	DTX-121210
7.9 (0.31)	2	304.8 (12.00)	x	304.8 (12.00)	x	304.8 (12.00)	37.2 (82.00)	14.1 (31.00)	DTX-121212
6.4 (0.25)	3/4	101.6 (4.00)	x	203.2 (8.00)	x	101.6 (4.00)	15.9 (35.00)	5.9 (13.00)	DTX-140804
6.4 (0.25)	3/4	101.6 (4.00)	x	203.2 (8.00)	x	152.4 (6.00)	18.1 (40.00)	6.8 (15.00)	DTX-140806
6.4 (0.25)	3/4	101.6 (4.00)	x	203.2 (8.00)	x	203.2 (8.00)	23.6 (52.00)	9.1 (20.00)	DTX-140808
7.9 (0.31)	2	101.6 (4.00)	x	101.6 (4.00)	x	152.4 (6.00)	34.0 (75.00)	12.7 (28.00)	DTX-141406
7.9 (0.31)	2	101.6 (4.00)	x	101.6 (4.00)	x	203.2 (8.00)	38.6 (85.00)	14.5 (32.00)	DTX-141408

① Type DTX boxes must have a minimum of 3-1/2 full threads at all conduit entrances. The "Max. Conduit Size" listed herein indicates the maximum drilled and tapped conduit entrance which can be machined into the four unbossed sides of a given box to provide these 3-1/2 full threads. If larger conduit openings than those listed herein are required, bosses can be supplied by us at an additional cost to provide the minimum 3-1/2 full thread requirement. In addition to the minimum 3-1/2 full thread requirement, the length of thread at conduit entrances must also be at least 1/4". A 3/8" conduit entrance therefore requires a minimum of a 6.4 mm (0.25") wall thickness. For aluminum box and cover, add suffix -A.

# DTX Series Junction Box Mounting Plate Information

## Dust-Ignitionproof, Watertight

Cast iron box and cover for surface mounting. Cast aluminum box and cover for surface mounting.


**NEC:**  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
NEMA 4, 9EFG

Mounting plates are used for mounting equipment up off the back of an enclosure. Steel Plates are all 3.3 mm (0.13") thick hot dip galvanized material. Aluminum plates are 3.3 mm (0.13") thick material up to and including 304.8 x 304.8 mm (12 x 12") size. All larger sizes are constructed of 4.8 mm (0.19") thick aluminum plate. The catalog numbers shown in the table below include the mounting buttons.

Select mounting plates based on inside length and width of box. Order as a separate item immediately following the catalog number of the box as follows:

Example: Line 1 **DTX-181204**  
Line 2 **WYM-1812-1**

For mounting plates in smaller boxes than listed, use similar catalog number logic. Example: A steel mounting plate for a **DTX-040404** box would be **WYM-0404-1**. Pricing will be based upon a **WYM-0808-1** price.



Inside Length and Width of Junction Box in mm (in)	Catalog Number		Style	Dimension in Millimeters (Inches)			
	Steel Plates	Aluminum Plates		L	W	A	B
203.2 x 203.2 (8 x 8)	<b>WYM-0808-1</b>	<b>WYM-0808-1A</b>	1	171.5 (6.75)	171.5 (6.75)	152.4 (6.00)	152.4 (6.00)
254.0 x 203.2 (10 x 8)	<b>WYM-1008-1</b>	<b>WYM-1008-1A</b>	1	222.3 (8.75)	171.5 (6.75)	203.2 (8.00)	203.2 (8.00)
254.0 x 254.0 (10 x 10)	<b>WYM-1010-1</b>	<b>WYM-1010-1A</b>	1	222.3 (8.75)	222.3 (8.75)	203.2 (8.00)	203.2 (8.00)
304.8 x 203.2 (12 x 8)	<b>WYM-1208-1</b>	<b>WYM-1208-1A</b>	1	273.1 (10.75)	171.5 (6.75)	254.0 (10.00)	152.4 (6.00)
304.8 x 254.0 (12 x 10)	<b>WYM-1210-1</b>	<b>WYM-1210-1A</b>	1	273.1 (10.75)	222.3 (8.75)	254.0 (10.00)	203.2 (8.00)
304.8 x 304.8 (12 x 12)	<b>WYM-1212-1</b>	<b>WYM-1212-1A</b>	1	273.1 (10.75)	273.1 (10.75)	254.0 (10.00)	254.0 (10.00)
355.6 x 203.2 (14 x 8)	<b>WYM-1408-1</b>	<b>WYM-1408-1A</b>	1	323.9 (12.75)	171.5 (6.75)	304.8 (12.00)	152.4 (6.00)
355.6 x 355.6 (14 x 14)	<b>WYM-1414-1</b>	<b>WYM-1414-1A</b>	1	323.9 (12.75)	323.9 (12.75)	304.8 (12.00)	304.8 (12.00)
406.4 x 203.2 (16 x 8)	<b>WYM-1608-1</b>	<b>WYM-1608-1A</b>	1	374.7 (14.75)	171.5 (6.75)	355.6 (14.00)	152.4 (6.00)
406.4 x 304.8 (16 x 12)	<b>WYM-1612-1</b>	<b>WYM-1612-1A</b>	1	374.7 (14.75)	273.1 (10.75)	355.6 (14.00)	254.0 (10.00)
406.4 x 406.4 (16 x 16)	<b>WYM-1616-1</b>	<b>WYM-1616-1A</b>	1	374.7 (14.75)	374.7 (14.75)	355.6 (14.00)	355.6 (14.00)
457.2 x 203.2 (18 x 8)	<b>WYM-1808-1</b>	<b>WYM-1808-1A</b>	1	171.5 (16.75)	171.5 (6.75)	152.4 (16.00)	152.4 (6.00)
457.2 x 254.0 (18 x 10)	<b>WYM-1810-1</b>	<b>WYM-1810-1A</b>	1	171.5 (16.75)	222.3 (8.75)	406.4 (16.00)	203.2 (8.00)
457.2 x 304.8 (18 x 12)	<b>WYM-1812-1</b>	<b>WYM-1812-1A</b>	1	171.5 (16.75)	273.1 (10.75)	406.4 (16.00)	254.0 (10.00)
457.2 x 355.6 (18 x 14)	<b>WYM-1814-1</b>	<b>WYM-1814-1A</b>	1	171.5 (16.75)	323.9 (12.75)	406.4 (16.00)	304.8 (12.00)
457.2 x 406.4 (18 x 16)	—	—	—	—	—	—	—
457.2 x 457.2 (18 x 18)	<b>WYM-1818-1</b>	<b>WYM-1818-1A</b>	1	171.5 (16.75)	171.5 (16.75)	406.4 (16.00)	406.4 (16.00)
508.0 x 254.0 (20 x 10)	<b>WYM-2010-1</b>	<b>WYM-2010-1A</b>	1	222.3 (18.75)	222.3 (8.75)	457.2 (18.00)	203.2 (8.00)
609.6 x 304.8 (24.00 x 12.00)	<b>WYM-2412-1</b>	<b>WYM-2412-1A</b>	2	552.5 (21.75)	247.7 (9.75)	533.4 (21.00)	228.6 (9.00)
609.6 x 457.2 (24.00 x 18.00)	<b>WYM-2418-1</b>	<b>WYM-2418-1A</b>	2	552.5 (21.75)	400.1 (15.75)	533.4 (21.00)	381.0 (15.00)
609.6 x 609.6 (24.00 x 24.00)	<b>WYM-2424-1</b>	<b>WYM-2424-1A</b>	3	552.5 (21.75)	552.5 (21.75)	533.4 (21.00)	533.4 (21.00)
711.2 x 304.8 (28.00 x 12.00)	<b>WYM-2812-1</b>	<b>WYM-2812-1A</b>	2	654.1 (25.75)	247.7 (9.75)	635.0 (25.00)	228.6 (9.00)
762.0 x 304.8 (30.00 x 12.00)	<b>WYM-3012-1</b>	<b>WYM-3012-1A</b>	2	704.9 (27.75)	247.7 (9.75)	685.8 (27.00)	228.6 (9.00)
762.0 x 457.2 (30.00 x 18.00)	<b>WYM-3018-1</b>	<b>WYM-3018-1A</b>	2	704.9 (27.75)	400.1 (15.75)	685.8 (27.00)	381.0 (15.00)
762.0 x 609.6 (30.00 x 24.00)	<b>WYM-3024-1</b>	<b>WYM-3024-1A</b>	3	704.9 (27.75)	552.5 (21.75)	685.8 (27.00)	533.4 (21.00)
914.4 x 304.8 (36.00 x 12.00)	<b>WYM-3612-1</b>	<b>WYM-3612-1A</b>	2	857.3 (33.75)	247.7 (9.75)	838.2 (33.00)	228.6 (9.00)
914.4 x 457.2 (36.00 x 18.00)	<b>WYM-3618-1</b>	<b>WYM-3618-1A</b>	2	857.3 (33.75)	400.1 (15.75)	838.2 (33.00)	381.0 (15.00)
914.4 x 609.6 (36.00 x 24.00)	<b>WYM-3624-1</b>	<b>WYM-3624-1A</b>	3	857.3 (33.75)	552.5 (21.75)	838.2 (33.00)	533.4 (21.00)
914.4 x 762.0 (36.00 x 30.00)	<b>WYM-3630-1</b>	<b>WYM-3630-1A</b>	3	857.3 (33.75)	704.9 (27.75)	838.2 (33.00)	685.8 (27.00)
914.4 x 914.4 (36.00 x 36.00)	<b>WYM-3636-1</b>	<b>WYM-3636-1A</b>	3	857.3 (33.75)	857.3 (33.75)	838.2 (33.00)	838.2 (33.00)

ENCLOSURES AND JUNCTION BOXES: NEC/CEC WEATHERPROOF/DUSTPROOF JUNCTION AND OUTLET BOXES



# DTX Series Junction Box Drill and Tap Schedule

## Dust-Ignitionproof, Watertight

Cast iron box and cover for surface mounting. Cast aluminum box and cover for surface mounting.

**NEC:**

Class II, Division 1 and 2, Groups E, F, G

Class III

NEMA 4, 9EFG

CONDUIT POSITION	CHECK ONLY IF FACTORY IS TO LOCATE			METAL PLUGS
	CONDUIT SIZE	X DIM.	D DIM.	
1				
2				
3				
4				
5				
6				
7				
8				
9				
10				
11				
12				
13				
14				
15				
16				
17				
18				
19				
20				
21				
22				
23				
24				

\* = B&D LOC.

VIEW LOOKING INTO BOX  
WITH SIDES LAID DOWN

**CHECK LIST**

ARE INDICATED CONDUIT SIZES WITHIN THE CATALOG PUBLISHED MAXIMUM ON PAGES K-40 AND K-43?

CHECK FOR MINIMUM SPACING BETWEEN CONDUIT OPENINGS PER CONDUIT SPACING TABLE, ON PAGE K-41.

SIGN NAME TO DWG.

NAME \_\_\_\_\_

DATE \_\_\_\_\_

**ENCLOSURE FIGURE**

ENCLOSURE

\* = BREATHER/DRAIN LOC. 1/2" NPT REQUIRED. LOCATION MAY BE SPECIFIED ON THE CHART OR IF BOX IS CHECKED, FACTORY WILL LOCATE IN SIDES A & C.

DIM. X = DISTANCE FROM CENTERLINE TO CENTER OF CONDUIT OPENING.  
DIM. D = DISTANCE FROM MTG. SURFACE TO CENTER OF CONDUIT OPENING.

HINGED ENCLOSURES WILL BE HINGED ON SIDE "D" AS STANDARD.

CAUTION: IN PLANNING CONDUIT ARRANGEMENTS, REFER TO "USABLE CONDUIT AREA", SHOWN ON THE APPROPRIATE PRODUCT OUTLINE DRAWINGS AND TO THE CONDUIT SPACING CHARTS.

CONDUIT D&T SCHEDULE	
CAT. NO. _____	REV _____

ENCLOSURES AND JUNCTION BOXES: NEC/CEC WEATHERPROOF/DUSTPROOF JUNCTION AND OUTLET BOXES



# DTX Series Junction Box

## Dust-Ignitionproof, Watertight

Cast iron box and cover for surface mounting. Cast aluminum box and cover for surface mounting.

**NEC:**  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 NEMA 4, 9EFG

### Outside Flange Dimensional Data in Millimeters (Inches)

Overall Enclosure				Mounting Enclosure			Mount Thick-ness	Depth	Conduit Area				Clear Opening		Wall Thickness			Catalog Number
A	B	C	D	E	F	G	J	K	L	M	N	P	S	T	X	Y	Z	
198.40 (7.81)	300.00 (11.81)	113.50 (4.47)	107.20 (4.22)	193.8 (7.63)	177.80 (7.00)	9.70 (0.38)	6.40 (0.25)	101.60 (4.00)	241.30 (9.50)	82.60 (3.25)	139.70 (5.50)	12.70 (0.50)	152.40 (6.00)	254.0 (10.00)	5.60 (0.22)	6.40 (0.25)	5.60 (0.22)	DTX-010604
198.40 (7.81)	300.00 (11.81)	164.30 (6.47)	158.00 (6.22)	193.8 (7.63)	177.80 (7.00)	9.70 (0.38)	6.40 (0.25)	152.40 (6.00)	241.30 (9.50)	133.40 (5.25)	139.70 (5.50)	12.70 (0.50)	152.40 (6.00)	254.0 (10.00)	5.60 (0.22)	6.40 (0.25)	5.60 (0.22)	DTX-100606
255.50 (10.06)	325.40 (12.81)	1029.50 (40.53)	108.00 (4.25)	2305.1 (90.75)	177.80 (7.00)	9.70 (0.38)	6.40 (0.25)	101.60 (4.00)	241.30 (9.50)	82.60 (3.25)	190.50 (7.50)	12.70 (0.50)	203.20 (8.00)	254.0 (10.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-100804
255.50 (10.06)	3049.50 (120.06)	215.10 (8.47)	158.80 (6.25)	2305.1 (90.75)	177.80 (7.00)	9.70 (0.38)	6.4 (0.25)	152.40 (6.00)	241.30 (9.50)	133.40 (5.25)	190.50 (7.50)	12.70 (0.50)	203.20 (8.00)	254.0 (10.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-100806
255.50 (10.06)	3049.50 (120.06)	2045.50 (80.53)	209.60 (8.25)	2305.1 (90.75)	177.80 (7.00)	9.70 (0.38)	6.4 (0.25)	203.20 (8.00)	238.30 (9.38)	184.20 (7.25)	187.50 (7.38)	12.70 (0.50)	203.20 (8.00)	254.0 (10.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-100808
255.50 (10.06)	3049.50 (120.06)	1029.50 (40.53)	108.00 (4.25)	295.4 (11.63)	177.80 (7.00)	9.70 (0.38)	6.40 (0.25)	101.60 (4.00)	241.30 (9.50)	82.60 (3.25)	241.30 (9.50)	12.70 (0.50)	254.00 (10.00)	254.0 (10.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-101004
255.50 (10.06)	3049.50 (120.06)	1537.50 (60.53)	158.80 (6.25)	295.4 (11.63)	177.80 (7.00)	9.70 (0.38)	6.40 (0.25)	152.40 (6.00)	241.30 (9.50)	133.40 (5.25)	241.30 (9.50)	12.70 (0.50)	254.00 (10.00)	254.0 (10.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-101006
306.30 (12.06)	3049.50 (120.06)	2045.50 (80.53)	209.60 (8.25)	295.4 (11.63)	177.80 (7.00)	9.70 (0.38)	6.40 (0.25)	203.20 (8.00)	238.30 (9.38)	184.20 (7.25)	238.30 (9.38)	12.70 (0.50)	254.00 (10.00)	254.0 (10.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-101008
153.90 (6.06)	3557.50 (140.06)	114.30 (4.50)	108.00 (4.25)	136.70 (5.38)	203.20 (8.00)	9.70 (0.38)	6.40 (0.25)	101.60 (4.00)	292.10 (11.50)	82.60 (3.25)	88.90 (3.50)	12.70 (0.50)	101.60 (4.00)	304.8 (12.00)	6.40 (0.25)	6.40 (0.25)	6.40 (0.25)	DTX-120404
204.70 (8.06)	3557.50 (140.06)	1029.50 (40.53)	108.00 (4.25)	212.90 (8.38)	203.20 (8.00)	11.20 (0.44)	6.40 (0.25)	101.60 (4.00)	292.10 (11.50)	82.60 (3.25)	139.70 (5.50)	12.70 (0.50)	152.40 (6.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-120604
204.70 (8.06)	3557.50 (140.06)	1537.50 (60.53)	158.80 (6.25)	212.90 (8.38)	203.20 (8.00)	11.20 (0.44)	6.40 (0.25)	152.40 (6.00)	292.10 (11.50)	133.40 (5.25)	139.70 (5.50)	12.70 (0.50)	152.40 (6.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-120606
255.50 (10.06)	357.10 (14.06)	115.00 (4.53)	108.00 (4.25)	263.70 (10.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	101.60 (4.00)	292.10 (11.50)	82.60 (3.25)	190.50 (7.50)	12.7 (0.50)	203.20 (8.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-120804
255.50 (10.06)	357.10 (14.06)	165.90 (6.53)	158.80 (6.25)	263.70 (10.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	152.40 (6.00)	292.10 (11.50)	113.40 (5.25)	190.50 (7.50)	12.70 (0.50)	203.20 (8.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-120806
255.50 (10.06)	357.10 (14.06)	216.70 (8.53)	209.60 (8.25)	263.70 (10.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	203.20 (8.00)	289.10 (11.38)	184.20 (7.25)	187.50 (7.38)	12.70 (0.50)	203.20 (8.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-120808
306.30 (12.06)	357.10 (14.06)	115.00 (4.53)	108.00 (4.25)	314.50 (12.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	101.60 (4.00)	292.10 (11.50)	82.60 (3.25)	241.30 (9.50)	12.70 (0.50)	254.00 (10.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-121004
306.30 (12.06)	357.10 (14.06)	165.90 (6.53)	158.80 (6.25)	314.50 (12.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	152.40 (6.00)	292.10 (11.50)	113.40 (5.25)	241.30 (9.50)	12.70 (0.50)	254.00 (10.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-121006
306.30 (12.06)	357.10 (14.06)	216.70 (8.53)	209.60 (8.25)	314.50 (12.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	203.20 (8.00)	292.10 (11.50)	184.20 (7.25)	238.30 (9.38)	12.70 (0.50)	254.00 (10.00)	304.8 (12.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-121008
357.10 (14.06)	357.10 (14.06)	115.80 (4.56)	108.00 (4.25)	365.30 (14.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	101.60 (4.00)	289.10 (11.38)	81.00 (3.19)	292.10 (11.50)	12.70 (0.50)	304.80 (12.00)	304.8 (12.00)	6.40 (0.25)	7.90 (0.31)	6.40 (0.25)	DTX-121204
357.10 (14.06)	357.10 (14.06)	166.60 (6.56)	158.80 (6.25)	365.30 (14.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	127.00 (5.00)	292.10 (11.50)	131.80 (5.19)	292.10 (11.50)	12.70 (0.50)	304.80 (12.00)	304.8 (12.00)	6.40 (0.25)	7.90 (0.31)	6.40 (0.25)	DTX-121206
357.10 (14.06)	357.10 (14.06)	193.80 (7.63)	185.70 (7.31)	365.30 (14.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	177.80 (7.00)	289.10 (11.38)	157.20 (6.19)	289.10 (11.38)	14.20 (0.56)	304.80 (12.00)	304.8 (12.00)	7.90 (0.31)	7.90 (0.31)	7.90 (0.31)	DTX-121207
357.10 (14.06)	357.10 (14.06)	219.20 (8.63)	211.10 (8.31)	365.30 (14.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	203.20 (8.00)	289.10 (11.38)	182.60 (7.19)	289.10 (11.38)	14.20 (0.56)	304.80 (12.00)	304.8 (12.00)	7.90 (0.31)	7.90 (0.31)	7.90 (0.31)	DTX-121208
357.10 (14.06)	357.10 (14.06)	270.00 (10.63)	261.90 (10.31)	365.30 (14.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	254.00 (10.00)	285.80 (11.25)	233.40 (9.19)	285.80 (11.25)	14.20 (0.56)	304.80 (12.00)	304.8 (12.00)	7.90 (0.31)	7.90 (0.31)	7.90 (0.31)	DTX-121210
357.10 (14.06)	357.10 (14.06)	320.80 (12.63)	312.70 (12.31)	365.30 (14.38)	203.20 (8.00)	10.90 (0.43)	9.70 (0.38)	304.80 (12.00)	285.80 (11.25)	284.20 (11.19)	285.80 (11.25)	14.20 (0.56)	304.80 (12.00)	304.8 (12.00)	7.90 (0.31)	7.90 (0.31)	7.90 (0.31)	DTX-121212
255.50 (10.06)	407.90 (16.06)	115.00 (4.53)	108.00 (4.25)	263.70 (10.38)	254.00 (10.00)	10.90 (0.43)	9.70 (0.38)	101.60 (4.00)	336.60 (13.25)	76.20 (3.00)	184.20 (7.25)	16.00 (0.63)	203.20 (8.00)	355.60 (14.00)	6.40 (0.25)	7.10 (0.28)	6.40 (0.25)	DTX-140804

ENCLOSURES AND JUNCTION BOXES: NEC/CEC WEATHERPROOF/DUSTPROOF JUNCTION AND OUTLET BOXES

