


BRASS DRILLING AND CUT-OFF HAMMERS

Our brass hammer line is non-marring and non sparking.

Fiberglass Handles

Fiberglass Handles provide exceptional breaking resistance to overstrikes. They are long-lasting and colored in high-visibility yellow. Our fiberglass handles have a non-slip safety grip.

Drilling and Cut-off Hammers are also available in Bronze/Copper. Please see page 13.



ABC2BFS - 2 lb / 0.90kg - 8" handle



ABC3BFS - 3 lb / 1.35kg - 8" handle



ABC4BFS - 4 lb / 1.80kg - 8" handle



ABC5BFS - 5 lb / 2.25kg - 8" handle



ABCWBW - 2.5 lb / 1.10kg - 12" handle

BRASS HAMMER SPECIFICATIONS

Our brass hammer line is non-marring and non sparking.

Brass Striking Hammers

Item #	Head Weight (lbs/kg)	Handle	Handle Length
ABC1BW	0.5 lbs/0.23 kg	Wood	10"/255mm
ABC1.5BW	1.5 lbs/0.68 kg	Wood	12.5"/320mm
ABC2BW	2.0 lbs/0.90 kg	Wood	12.5"/320mm
ABC3BW	3.0 lbs/1.35 kg	Wood	12.5"/320mm
ABC4BW	4.0 lbs/1.80 kg	Wood	15"/380mm
ABC5BW	5.0 lbs/2.25 kg	Wood	15"/380mm
ABC1BFB	1.0 lbs/0.45 kg	Fiberglass	10.5"/270mm
ABC1.5BFB	1.5 lbs/0.68 kg	Fiberglass	10.5"/270mm
ABC2BFB	2.0 lbs/0.90 kg	Fiberglass	12"/305mm
ABC3BFB	3.0 lbs/1.35 kg	Fiberglass	12"/305mm
ABC3BFB	3.0 lbs/1.35 kg	Fiberglass	14"/355mm
ABC4BFB	4.0 lbs/1.80 kg	Fiberglass	12"/305mm
ABC4BFB	4.0 lbs/1.80 kg	Fiberglass	14"/355mm
ABC5BFB	5.0 lbs/2.25 kg	Fiberglass	12"/305mm
ABC5BFB	5.0 lbs/2.25 kg	Fiberglass	14"/355mm
ABC6BFB	6.0 lbs/2.70 kg	Fiberglass	13.5"/345mm

Brass Drilling Hammers

Item #	Head Weight (lbs/kg)	Handle	Handle Length
ABC2BFS	2.0 lbs/0.90 kg	Fiberglass	8"/205mm
ABC3BFS	3.0 lbs/1.35 kg	Fiberglass	8"/205mm
ABC4BFS	4.0 lbs/1.80 kg	Fiberglass	8"/205mm
ABC5BFS	5.0 lbs/2.25 kg	Fiberglass	8"/205mm

Brass Sledge Hammers

Item #	Head Weight (lbs/kg)	Handle	Handle Length
ABC6BWS	6.0 lbs/2.70 kg	Wood	21"/535mm
ABC6BW	6.0 lbs/2.70 kg	Wood	32"/810mm
ABC8BWS	8.0 lbs/3.60 kg	Wood	21"/535mm
ABC8BW	8.0 lbs/3.60 kg	Wood	32"/810mm
ABC10BWS	10.0 lbs/4.50 kg	Wood	21"/535mm
ABC10BW	10.0 lbs/4.50 kg	Wood	32"/810mm
ABC12BW	12.0 lbs/5.40 kg	Wood	32"/810mm
ABC14BW	14.0 lbs/6.30 kg	Wood	32"/810mm
ABC20BW	20.0 lbs/9.0 kg	Wood	32"/810mm
ABC6BFBS	6.0 lbs/2.70 kg	Fiberglass	21.5"/546mm
ABC6BF	6.0 lbs/2.70 kg	Fiberglass	33"/840mm
ABC8BFBS	8.0 lbs/3.6 kg	Fiberglass	22"/560mm
ABC8BF	8.0 lbs/3.6 kg	Fiberglass	33"/840mm
ABC10BFBS	10.0 lbs/4.50 kg	Fiberglass	22"/560mm
ABC10BF	10.0 lbs/4.50 kg	Fiberglass	33"/840mm
ABC12BF	12.0 lbs/5.40 kg	Fiberglass	33"/840mm
ABC14BF	14.0 lbs/6.30 kg	Fiberglass	33"/840mm
ABC20BF	20.0 lbs/9.0 kg	Fiberglass	33"/840mm

Brass Cut-Off Hammers

Item #	Head Weight (lbs/kg)	Handle	Handle Length
ABCWBW	2.5 lbs/1.10 kg	Wood	12"/304mm