DELAYED EGRESS PANIC LOCKS

715 Series - Stand alone delayed egress panic lock. 15 second delayed latch, instant alarm. Instant egress in case of emergency or fire. Meets NFPA 101 Life Safety Code. Includes monitoring output for secondary siren , CCTV or remote monitoring. Smoke detector input.

SPECIFICATIONS:

Cover: Die cast metal
Push bar: Extruded aluminum push bar and channel
Handed: Non-handed
Installation: Surface mounted for single or double doors
Cylinder: Accepts most standard size rim cylinder used for Inside and outside key control
Power: AC powered with 9v battery back-up for siren. Transformer And armored cable included
Lock bolt: 1" throw heavy die cast with reinforced steel inserts
Alarm: Dual piezo siren measured at 95db

PRODUCT	DESCRIPTION	LIST PRICE
715X28X88	15 second delayed egress lock. Aluminum finish with monitoring output. 33" bar.	$1,078.00
715x28x88x48	15 second delayed egress lock. Aluminum finish with monitoring output. 48" bar	$1,091.00
CER-KD CER-12345	Standard rim cylinder	$32.00
725x28	Single door strike (included with unit)	$55.00
735x28	Double door strike (not included with unit)	$55.00
SWK-715	Surface wiring kit for wood or glass doors	$94.00
767x28	Metal mounting plate for glass doors	$22.00
277-12	277v transformer to wire 715 from Exit Sign	$65.00
271	Armored cable	$56.00

ELECTRIC DEADBOLTS

Models 103 & 104 **Fail-safe or fail-secure electric deadbolts. Available In 12v or 24v AC or DC. Perfect for use on narrow stile Doors. Complete with angle, mortise or flush mount strikes. Use with standard key or push button switch.**

SPECIFICATIONS:

Cover: Molded aluminum
Power : Requires 400 mA for 24v, 800mA for 12v unit
Deadbolt: Powered by a continuous duty solenoid. 5/8" diameter And 5/8" projection.

PRODUCT	DESCRIPTION	LIST PRICE
103	24v AC or DC. Includes three strikes and magnets. Fail-safe	$360.00
103x12	12v AC or DC. Includes three strikes and magnets. Fail-safe	$424.00
104RA	24v AC or DC. Includes three strikes and magnets. Fail-secure	$429.00
104x12	12v AC or DC. Includes three strikes and magnets. Fail-secure	$474.00
221 / 241	24v Plug-in style transformers	$55.00
222	24v Wire-in style transformer	$55.00