pe.eaton.com

NGR Rocker Switch Base

NGR15481BGYGN

UPC:786685575018

Dimensions:

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

Weight:8 LB

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Type:** No rocker assembled
- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 1548
- **Circuit Position Center:** NONE
- **Circuit Position Down:** ON
- **Contact Material:** Gold plated
- **Frame Color:** Black
- **Lamp Color:** Amber (top)-green (bottom)
- **Lamp Voltage:** 14V
- **Mounting:** Snap-in mounting
- **Number Of Poles:** Single-pole
- **Style:** Rocker and paddle frame
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- Eatons Volume 11-Vehicle and Commercial Controls

- Eaton Specification Sheet - NGR15481BGYGN

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.