Powering Business Worldwide

pe.eaton.com



# New Generation Rockers Switch Base

**NGR15831BNA0N**

**UPC:**786685467108

**Dimensions:**

- **Height:** 1.8 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

**Notes:**A lamp type is replaceable

**Warranties:**

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

**Specifications:**

- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 1583
- **Circuit Position Center:** OFF
- **Circuit Position Down:** MOM ON
- **Contact Material:** Standard plating
- **Frame Color:** Black
- **Lamp Color:** Clear
- **Lamp Voltage:** 14 Vdc incandescent
- **Mounting:** Snap-in
- **Number Of Poles:** Single-pole
- **Style:** Rocker and paddle frame
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

**Supporting documents:**

- Eatons Volume 11-Vehicle and Commercial Controls

- Eaton Specification Sheet - NGR15831BNA0N

**Certifications:**

- CSA Certified
- UL Listed

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.