HUBBELL
Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 3-Wire, 10A 600V AC, PA Wire Code, 10′ Length, Stainless Hex Nuts

By Hubbell Wiring Device-Kellems
Catalog # PG1003PA010S

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 3-Wire, 10A 600V AC, PA Wire Code, 10′ Length, Stainless Hex Nuts

Features

- Linkosity
- Cordset
- Female
- Double End

Application

Quick Connect/Disconnect Signal and Control

Specifications

EU RoHS Indicator	Yes

Conductor

Conductor Type	Copper
Strands	Multi
Number Of Conductors	3-Pole

Current

Amperage Rating	10 A
Voltage Rating	600V kV

Dimensions

Outside Diameter	0.71

General

Plug Type	Linkosity
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585184869
Color	Gray

Logistics

Carton Quantity	10

Operational

Temperature Rating	-20 Deg C to 105 Deg C

Product Assets

Catalog [English]
Installation Manual [English]

© 2026 Hubbell Incorporated. All rights reserved