HUBBELL
Wiring Device-Kellems

TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black, With Plate

By Hubbell Wiring Device-Kellems
Catalog # RR450WIPCN

TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black, With Plate

Features

- Single Panel Mount Receptacle
- 50A 125/250V
- 3-Pole 4-Wire Grounding

Application

Residential Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	14-50R

Conductor

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG Min #6 AWG Max
Number Of Poles	3-Pole

Current

Current Rating	50 A
Amperage Rating	50 A
Phase	Single Phase
Current / Amperage Rating	50 A
Connectivity	Screw Terminals
Wattage	12500
Voltage Rating	125/250 VAC

Dimensions

Display Size	Standard Sized Product

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Flanged Single
Material - Mounting Hardware	Screw Mounting
Material	Thermoplastic
UPC	883778301865

Logistics

Carton Quantity	10

Product Assets

Catalog [English]
Installation Manual [Spanish, French, English]

© 2026 Hubbell Incorporated. All rights reserved