Tubular Inside Micrometer with Extension

Item number: 140-161

Images



Description

This is a long range inside micrometer that offers you the following benefits:

- It has a long measuring range of up to 5000 mm
- Extension tube type design.
- Measuring surfaces in carbide are available, micro-lap finish

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	40 - 80 "
Measuring span:	2"
Graduation:	0.001"
Limit of error:	±(0,00035+0,00005xnumber of rods+0,00005(max. measurement length/2))"
Scale:	Thimble and sleeve satin chrome finish, ø21 mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Carbide
Extension rods:	5 (2, 4, (2 pcs.), 8, 20")
Delivered:	Including box, spanner, extension rods (5 pcs.), micrometer head
Spindle feed error:	0.0003 inch
Mass:	3900 g

Dimensions



Spare parts

Consumable spares:

Extension Rod 50mm, for Series 140

Art No. 04GZA394
Suggested retail price: **118.00 €***

Extension Rod 100mm, for Series 140

Art No. 04GZA396
Suggested retail price: **149.00 €***

Extension Rod 200mm, for Series 140

Art No. 04GZA398
Suggested retail price: **214.00 €***

Extension Rod 500mm, for Series 140

Art No. 04GZA400
Suggested retail price: **380.00 €***

Extension Rod 1000mm, for Series 140

Art No. 04GZA402
Suggested retail price: **529.00 €***