Mitutoyo

3-Point Internal Micrometer Holtest

Item number: 368-277

Images

Description

These are three-point and two-point internal micrometers that offer you the following benefits:

- Titanium-coated measuring pins give you excellent durability and impact resistance (3-point type).
- Three-point micrometer allows stable measurement through automatic centring.
- It is delivered without setting rings or extensions.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	7 - 8 "
Graduation:	≤ 0.5": 0.0001", >0.5": 0.0002"
Scale:	Thimble and sleeve satin chrome finish, Up to 0.5" : ø 17 mm Over 0.5" : ø 23 mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Titanium coated hardened steel Taper: tungsten carbide
Measuring method:	3-point
Delivered:	Including box, spanner, hex wrench, certificate of inspection, without setting ring
Mass:	1320 g

Dimensions



a: 12.4 mm

b: 21 mm

c: 13.8 mm

L1: 161 - 161 mm

L2: 227 - 252 mm



a: 12.4 mm

b: 21 mm

c: 13.8 mm

L1: 161 - 161 mm

L2: 227 - 252 mm

Accessories

Optional accessories:

Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: **216.00 €***

Setting Ring 7"

Steel
Art No. 177-303
Suggested retail price: **1,516.00 €***

Setting Ring 8"

Steel
Art No. 177-305
Suggested retail price: **1,929.00 €***