Mitutoyo

2-Point Inside Measuring Instrument

Item number: 526-153-20

Images

Description

This is a two point split contact point ideally suited to smaller bore measurements.
It offers you the following benefits:

- A precision bore gauge so you can make quick and accurate measurements of small hole diameters (0.95-18 mm).
- You can replace the analogue indicator fitted to this instrument with a customer-supplied Digimatic indicator if you need.
- The contact point is hard chrome coated.

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	3.7 - 7.3 mm
Graduation:	0.01mm
Accuracy:	4 µm
Repeatability:	2 µm
Measuring depth:	32 mm
No. Dial Indicator:	2046AB
Number of anvils:	7
Delivered:	In a box, with dial indicator and cover for dial indicator, without setting ring
Mass:	240 g

Dimensions



Accessories

Optional accessories:

Stand for Bore Gauge Series 526

D=60mm Table, 38mm Table Stroke
Art No. 215-120-10
Suggested retail price: **1,178.00 €***

Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate
Art No. 543-310B-10
Suggested retail price: **563.00 €***

Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

Standard accessories:

Promotion!

Dial Gauge, Flat Back, ISO Type

10mm, 0,01mm
Art No. 2046AB
Promo price: **37.90 €***
~~Suggested retail price: **48.00 €***~~

Protector for Indicator (plastic cover)

Art No. 21DZA000
Suggested retail price: **20.00 €***