2-Point Inside Measuring Instrument

Item number: 526-155-11

Images

Description

This is a two point split contact point ideally suited to smaller bore measurements.
It offers you the following benefits:

- A precision bore gauge so you can make quick and accurate measurements of small hole diameters (0.95-18 mm).
- You can replace the analogue indicator fitted to this instrument with a customer-supplied Digimatic indicator if you need.
- The contact point is hard chrome coated.

Features

Repeatability:	2 µm
Delivered:	In a box, without dial indicator and cover for dial indicator, with setting ring

Dimensions



Accessories

Optional accessories:

Stand for Bore Gauge Series 526

D=60mm Table, 38mm Table Stroke
Art No. 215-120-10
Suggested retail price: **1,178.00 €***

Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005", Flat Back Plate
Art No. 543-312B-10
Suggested retail price: **563.00 €***

Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

Standard accessories:

Art No. 177-364
Price on application

Setting Ring 0,18"

Steel
Art No. 177-365
Suggested retail price: **126.00 €***

Setting Ring 0,2"

Steel
Art No. 177-366
Suggested retail price: **126.00 €***

Setting Ring 0,22"

Steel
Art No. 177-367
Suggested retail price: **126.00 €***

Art No. 177-368
Price on application

Setting Ring 0,26"

Steel
Art No. 177-369
Suggested retail price: **126.00 €***

Setting Ring 0,28"

Steel
Art No. 177-370
Suggested retail price: **126.00 €***