

PT Platforms

Quality construction with diamond-plate surface for ultimate durability and performance



Features

- Rugged construction stands up to industrial use
- Diamond-plate surface for added grip
- Optional ramps facilitate loading and unloading
- Can be used with any Adam indicators
- Approximately five-meter/15-foot shielded cable



AE 403 Indicator
see pg. 46



AE 503 & AE 504 Indicator
see pg. 47



GK & GC Indicator
see pg. 48

General Specifications

- Weighing units: kg, lb*
 - Housing: Mild steel base
 - Operating temperature: -10° to 40°C / 14° to 104°F
- *Not all weighing units available on select indicator setups

Applications

- Weighing
- Parts counting
- Checkweighing
- Dynamic / Animal weighing



WARRANTY
12
MONTHS

Base Only

Model	Capacity	Readability	Platform Size	Shipping Weight	Shipping Dimensions	Price
PT 110	2500lb / 1000kg	0.5lb / 0.2kg	39.4"x39.4" / 1000x1000mm	172lb / 82kg	41"x41"x10" / 1041x1041x254mm	\$795.00
PT 310-5	5000lb / 3000kg	1lb / 0.5kg	39.4"x39.4" / 1000x1000mm	198.9lb / 90.26kg	41"x41"x10" / 1041x1041x254mm	\$795.00
PT 310-10	10000lb / 4500kg	2lb / 1kg	39.4"x39.4" / 1000x1000mm	198.9lb / 90.26kg	41"x41"x10" / 1041x1041x254mm	\$795.00
PT 112	2500lb / 1000kg	0.5lb / 0.2kg	47.2"x47.2" / 1200x1200mm	208.9lb / 94.8kg	48"x48"x10" / 1219x1219x254mm	\$995.00
PT 312-5	5000lb / 3000kg	1lb / 0.5kg	47.2"x47.2" / 1200x1200mm	263.9lb / 119.75kg	48"x48"x10" / 1219x1219x254mm	\$995.00
PT 312-10	10000lb / 4500kg	2lb / 1kg	47.2"x47.2" / 1200x1200mm	263.9lb / 119.75kg	48"x48"x10" / 1219x1219x254mm	\$995.00
PT 115	2500lb / 1000kg	0.5lb / 0.2kg	59.1"x59.1" / 1500x1500mm	278.9lb / 126.55kg	61"x61"x10" / 1549x1549x254mm	\$1195.00
PT 315-5	5000lb / 3000kg	1lb / 0.5kg	59.1"x59.1" / 1500x1500mm	375.9lb / 170.55kg	61"x61"x10" / 1549x1549x254mm	\$1195.00
PT 315-10	10000lb / 4500kg	2lb / 1kg	59.1"x59.1" / 1500x1500mm	375.9lb / 170.55kg	61"x61"x10" / 1549x1549x254mm	\$1195.00

Approved Base Only

Model	Capacity	Readability	Platform Size	Shipping Weight	Shipping Dimensions	Price
PT 112M	2500lb / 1500kg	0.5lb / 0.2kg	47.2"x47.2" / 1200x1200mm	214.9lb / 97.52kg	48"x48"x18" / 1219x1219x457mm	\$1050.00
PT 312-5M	5000lb / 3000kg	1lb / 0.5kg	47.2"x47.2" / 1200x1200mm	263.9lb / 119.75kg	48"x48"x10" / 1219x1219x254mm	\$1050.00

Product details continued on next page >>