

GBK Bench Checkweighing Scales

The best solution for demanding industrial and manufacturing tasks



Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Capacity tracker built into display for easily monitoring possible overloads
- Checkweighing LEDs light to clearly show under, over and acceptable limits
- Checkweighing with audible alarm
- Parts counting with freely selectable sample sizes
- Hold function freezes the displayed weight, allowing time to lapse without losing the result
- Large, grade 304 stainless steel pan allows swift cleaning
- Sealed keypad protects against dirt and accidental spills
- Audible overload alarm warns when capacity has been exceeded
- RS-232 interface for connection to computers and printers
- Rechargeable battery included for operation almost anywhere

General Specifications

- Weighing units: g, kg, lb, lb:oz, oz
- Interface: RS-232
- Power Supply: 12VDC 800mA adapter / Internal rechargeable battery
- Display: Backlit LCD with 20mm-high digits
- Calibration: External calibration
- Housing: ABS plastic
- Operating Temperature: -10° to 40°C / 14° to 104°F

Model	Capacity	Readability	Pan Size	Price
GBK 16a	16lb / 8kg	0.0002lb / 0.1g	11.8"x15.7" / 300x400mm	\$575.00
GBK 35a	35lb / 16kg	0.001lb / 0.5g	11.8"x15.7" / 300x400mm	\$475.00
GBK 70a	70lb / 32kg	0.002lb / 1g	11.8"x15.7" / 300x400mm	\$525.00
GBK 130a	130lb / 60kg	0.005lb / 2g	11.8"x15.7" / 300x400mm	\$525.00
GBK 260a	260lb / 120kg	0.01lb / 5g	11.8"x15.7" / 300x400mm	\$555.00

Applications

- Weighing
- Parts counting
- Percentage weighing
- Checkweighing
- Dynamic / animal weighing
- Accumulation

NTEP/Measurement Canada Approved

Model	Capacity	Readability	Pan Size	Price
GBK 15aM	15lb / 6kg	0.002lb / 1g	11.8"x15.7" / 300x400mm	\$650.00
GBK 30aM	30lb / 15kg	0.005lb / 2g	11.8"x15.7" / 300x400mm	\$550.00
GBK 60aM	60lb / 30kg	0.01lb / 5g	11.8"x15.7" / 300x400mm	\$600.00
GBK 150aM	150lb / 60kg	0.02lb / 0.01kg	11.8"x15.7" / 300x400mm	\$600.00
GBK 300aM	300lb / 150kg	0.05lb / 0.02kg	11.8"x15.7" / 300x400mm	\$630.00



Accessories

Item number	Description	Price
• 3052010526	In-use wet cover	\$20.00
• 3074010266	RS-232 cable (null-modem)	\$35.00
• 3074010507	RS-232 to USB adapter (must order corresponding RS-232 cable)	\$50.00
• 1120011156	ATP thermal printer	\$335.00
• 3126011263	Thermal paper (for item no. 1120011156-ATP printer)	\$14.00
• 3126011281	Thermal paper (pack of 10) (for item no. 1120011156-ATP printer)	\$90.00
• 600002028	Adam DU data collection program	\$95.00
•	Calibration certificate	Contact Us