

TABLE MOUNTED
STAINLESS STEEL SHELVING
with Adjustable Chrome Posts



Item #: _____ Qty #: _____

Model #: _____

Project #: _____



(Table Not Included)



TS & DS SERIES includes
Tapered Split Sleeve Installation

FEATURES:

Fully adjustable stainless steel shelving.
Includes four 14" or 34" high Chrome Posts.
Includes 4 Plastic Tapered Split Sleeve Mounting Brackets.
Shelves have front & rear rolled edges and sides have square edges.

CONSTRUCTION:

All TIG welded.
Exposed surfaces polished to a satin finish.

MATERIAL:

All Shelves are 18 gauge type "430" stainless steel.



TS SERIES
14" Adjustable Chrome Posts



DS SERIES
34" Adjustable Chrome Posts

Size (W x L)	SINGLE Model #	Approx. Weight	DOUBLE Model #	Approx. Weight
12" x 36"	TS-12-36	16 lbs.	DS-12-36	28 lbs.
12" x 48"	TS-12-48	18 lbs.	DS-12-48	33 lbs.
12" x 60"	TS-12-60	20 lbs.	DS-12-60	39 lbs.
12" x 72"	TS-12-72	22 lbs.	DS-12-72	44 lbs.
12" x 84"	TS-12-84	26 lbs.	DS-12-84	50 lbs.
12" x 96"	TS-12-96	33 lbs.	DS-12-96	59 lbs.
12" x 108"	TS-12-108	37 lbs.	DS-12-108	64 lbs.
12" x 120"	TS-12-120	41 lbs.	DS-12-120	70 lbs.
12" x 132"	TS-12-132	45 lbs.	DS-12-132	76 lbs.
12" x 144"	TS-12-144	51 lbs.	DS-12-144	82 lbs.

Units 8 ft. and larger are furnished with
three (3) sets of tubing supports.

For 1" Rear Turn Up, add "R" after model #
(Example: TS-12-60R or DS-12-60R)


DETAILS and SPECIFICATIONS

TOL $\pm .500"$

ALL DIMENSIONS ARE TYPICAL



TS SERIES: ADJUSTABLE SINGLE SHELF WITH TABLE MOUNTED 14" CHROME POSTS

Specify location. Front, Center or Rear.



DS SERIES: ADJUSTABLE DOUBLE SHELVES WITH TABLE MOUNTED 34" CHROME POSTS

Specify location. Front, Center or Rear.



Brass Expander Table
Mounting Hardware Included
with TS & DS Shelving
(1" tubing only)

