


Portable Pre-Filter

The 300 cfm pre-filter with auto-drain is designed to remove large amounts of oil and water discharged from a compressor before it enters the Breather Box®. The pre-filter will extend the Breather Box® filter life, reduce maintenance downtime and costs. Ideal for use in humid climates.



Key Details:

- High capacity 300 cfm bulk filtration and moisture removal - 200 psi rated with metal bowl
- Automatic drain assembly
- Galvanized steel frame with carry handle
- Supplied with 1/2" Chicago fitting on inlet, 1/2" Industrial Interchange socket on outlet
- Use after compressor and before Grade-D Air Filtration Breather Box®

Portable Pre-Filter

Item No.	Description
PF-240	High capacity portable compressor prefilter with stand, 300 cfm capacity, 1/2" Chicago inlet, and 1/2" 5000 series Hansen socket outlet, with auto drain
BB100-A	Replacement particulate filter for PF-240

Breathing Air Hose & Accessories



3/8" Breathing Air Hose - Black

Item No.	Description
H-6-3	6 foot length - 1/4" Hansen style fittings
H-10-3	10 foot length - 1/4" Hansen style fittings
H-25-3	25 foot length - 1/4" Hansen style fittings
H-50-3	50 foot length - 1/4" Hansen style fittings
H-100-3	100 foot length - 1/4" Hansen style fittings
H-300-3	300 foot length - 1/4" Hansen style fittings



1/2" Breathing Air Hose - Yellow

Item No.	Description
H-6-5	6 foot length - 1/2" Hansen style fittings
H-10-5	10 foot length - 1/2" Hansen style fittings
H-25-5	25 foot length - 1/2" Hansen style fittings
H-50-5	50 foot length - 1/2" Hansen style fittings
H-100-5	100 foot length - 1/2" Hansen style fittings
H-300-5	300 foot length - 1/2" Hansen style fittings

All hose length can be custom ordered or include other fitting types for an additional charge.



Polyethylene Hose Cover

3/4" Breathing Air Hose - Red

Item No.	Description
H-25-12	25 foot length - 1/2" Hansen style fittings
H-50-12	50 foot length - 1/2" Hansen style fittings
H-100-12	100 foot length - 1/2" Hansen style fittings

Contact Customer Service for a quote.

Polyethylene Hose Cover

Item No.	Description
LF2H	Polyethylene hose cover - fits 1/2" or 3/8" hose - 1125' roll



Whip Check

Whip Check Air Hose Safety Cable

Item No.	Description
ASWHIPLINE	Hose to Hose - fits OD 1/2" to 1 1/4" hose (20" length)
ASWHIPLN10	Hose to Hose - fits OD 1" to 2 1/2" hose (28" length)
ASWHIPLN15	Hose to Hose - fits OD 1 1/2" to 3" hose (38" length)
ASWHIPTL20	Hose to Tool - fits OD 1/2" to 1 1/4" hose (20" length)
ASWHIPTL38	Hose to Tool - fits OD 1 1/2" to 3" hose (38" length)