


Bi-Color Stack & Nest Totes

- Stack when loaded to protect contents, nest when empty with 180° turn - 50% nesting ratio.

- Available in solid and ventilated versions.
- Modular to 48" x 45" pallet.
- Compatible with automated handling equipment.
- Standard colors include Gray/Red, Gray/Blue, Gray/Green, Green/Blue, Lt. Blue/Blue.

Solid or vented styles for flexibility to fit applications from food to automotive parts

Bi-Colors clearly identify stack and nest positions: alternate colors - nested, same color - stacked



Straight walls provide maximum internal and external space usage

Smooth surfaces for easy cleaning

Identification areas for labels and tags



Unique, one-piece design allows for optional dividers, cradles, and dunnage.



SN15120709


SN24150709

SN24150999

SN24220913

SN24221113

Bi-Color Stack & Nest Totes



| Model No. | Outside Dimensions | | | | | | Inside Dimensions Bottom | | | | | | Capacity | |
|------------|--------------------|-----|----|-----|-----|-----|--------------------------|-----|-----|-----|-----|-----|----------|----|
| | Inches | | | mm | | | Inches | | | mm | | | Lbs. | Kg |
| | L | W | H | L | W | H | L | W | H | L | W | H | | |
| SN15120709 | 15 | 12 | 7½ | 381 | 305 | 191 | 11½ | 10¾ | 7 | 293 | 264 | 178 | 35 | 15 |
| SN24150709 | 24 | 15 | 7½ | 610 | 381 | 191 | 20½ | 13¾ | 7 | 521 | 340 | 178 | 35 | 15 |
| SN24150999 | 24 | 15 | 9½ | 610 | 381 | 240 | 20½ | 13¾ | 9 | 521 | 340 | 229 | 45 | 20 |
| SN24220913 | 24 | 22½ | 9 | 610 | 572 | 229 | 21¼ | 20½ | 8½ | 553 | 520 | 218 | 45 | 20 |
| SN24221113 | 24 | 22 | 11 | 610 | 559 | 279 | 21¼ | 20½ | 10¾ | 553 | 520 | 269 | 45 | 20 |
| 11020 | 23¾ | 15¼ | 4¾ | 600 | 400 | 117 | - | - | - | - | - | - | - | - |

KeepBoxes™


- KeepBoxes stack and nest for optimal space usage
- Clearly identify contents through transparent bases
- Attached lids snap securely closed to protect contents from dust or damage

Durable full-length steel hinge pins for lids



66497CLDGN

Ribbing reinforces sides to prevent flexing under loads



66486CLDBL

66499CLSIL

Tilt & Locks

| Model No. | Description | L | W | H | L | W | H | Ctn. Qty. |
|------------|-------------------|-----|-----|-----|-----|-----|-----|-----------|
| 66486CLDBL | 12-Gallon KeepBox | 21½ | 15 | 12½ | 546 | 381 | 318 | 6 |
| 66499CLSIL | 68-Quart KeepBox | 23 | 16¾ | 14 | 584 | 422 | 356 | 6 |
| 66497CLDGN | 18-Gallon KeepBox | 21½ | 15 | 17 | 546 | 381 | 432 | 3 |