



DELUXE SUPPLIED-AIR SHIELD AND BLACK WELDING HELMET

- Performance proven and a cost-effective system used by foundries, aluminum plants, mines, chemical plants, refineries, auto manufacturers, metal working, and fabrications
- Provides a constant and powerful supply of breathable air from a clean air source
- Provides protection from airborne contaminants including hexavalent chromium applications, flying debris, sparks, chemical, and molten metal splashes
- Visor flips up allowing user to grind and clean metal looking through clear ANSI face shield
- Designed to connect to low-pressure or high-pressure flow adapters
- Large #10 lens included
- Complies with ANSI Z89.1 Type 1 Class G for head protection
- Complied with ANSI Z87.1+ for face-shield/eye protection
- APF 1000
- **NIOSH approval TC-19C-0488**




Low Pressure	Order No.
Deluxe Supplied-Air Shield and Black Welding Helmet w/ No Flow Valve	9904-WB
Deluxe Supplied-Air Shield and Black Welding Helmet w/ LP Adapter	9904-DWB

High Pressure	Order No.
Deluxe Supplied-Air Shield and Black Welding Helmet w/ HP Personal Air Cooler	9904-CWB
Deluxe Supplied-Air Shield and Black Welding Helmet w/ HP Flow Control Valve	9904-CVWB
Deluxe Supplied-Air Shield and Black Welding Helmet w/ HP Air Temperature Controller	9904-HCWB

Accessories

Replacement Variable Shade #10 Lens Kit
Order No. 9904-35



Video available on the ALLEGRO INDUSTRIES Channel
www.youtube.com/AllegroIndustries

EZ AIR FLEX GRINDING/WELDING AIR SHIELD

- Intended for industrial applications where combined respiratory, eye, and face protection are required, such as welding, assembly, facility maintenance, grinding, machine operations, painting, and sanding
- Made from Dupont® super tough flame-retardant nylon that can withstand extreme cold/heat without cracking or deforming
- Features a durable flip-up visor to expose a grind shield below that maintains respiratory protection while workers continue grinding or inspecting welds
- Large shield design accommodates safety glasses under the face shield
- Adjustable durable Pera-Lok locking ratcheting headgear with replaceable ultrasoft sweat band
- Lightweight, comfortable, and easily replaceable 100% cotton FR treated face seal
- Visor dimension: 7" x 5.4" x 0.040"
- Viewing area: 41.2 sq. in.
- Lightweight at only 0.58 lbs. total
- Air tran directs air over the head and across the breathing zone, minimizing fogging
- User control of airflow direction
- APF 25
- Equipped with variable shade, auto-darkening lens, shade 5-14
- Complies with ANSI Z87.1+ for face-shield/eye protection
- CE certified
- **NIOSH approval TC-19C-0588**

Low Pressure	Order No.
EZ Air Flex Grinding/Welding Air Shield Headtop	9907-WADF
EZ Air Flex Grinding/Welding Air Shield Headtop w/ LP Adapter	9907-DWADF

High Pressure	Order No.
EZ Air Flex Grinding/Welding Air Shield Headtop w/ HP Flow Control Valve	9907-CWADF
EZ Air Flex Grinding/Welding Air Shield Headtop w/ HP Personal Air Cooler	9907-CWADF
EZ Air Flex Grinding/Welding Air Shield Headtop w/ HP Air Temperature Controller	9907-HCWADF

Accessories

Replacement Variable Shade
Order No. 9904-36

