

3/8" Square Drive Adapters



1/4" to 3/4" Male Square



Part Number	Male Square In.	Female Square In.	Type of Lock	Overall Length	
				In.	mm
EX-254	1/4	3/8	Pin	1 1/4	32
EX-254-B	1/4	3/8	Ball	1 1/4	32
EX-257-2	1/4	3/8	Pin	2	51
EX-257-B-2	1/4	3/8	Ball	2	51
EX-257-3	1/4	3/8	Pin	3	76
EX-257-B-3	1/4	3/8	Ball	3	76
EX-257-4	1/4	3/8	Pin	4	102
EX-257-B-4	1/4	3/8	Ball	4	102
EX-257-5	1/4	3/8	Pin	5	127
EX-257-B-5	1/4	3/8	Ball	5	127
EX-257-6	1/4	3/8	Pin	6	152
EX-257-B-6	1/4	3/8	Ball	6	152
EX-503	1/2	3/8	Pin	1 1/2	38
EX-503-B	1/2	3/8	Ball	1 1/2	38
EX-507-2	1/2	3/8	Pin	2	51
EX-507-3	1/2	3/8	Pin	3	76
EX-507-B-3	1/2	3/8	Ball	3	76
EX-507-4	1/2	3/8	Pin	4	102
EX-507-B-4	1/2	3/8	Ball	4	102
EX-507-6	1/2	3/8	Pin	6	152
EX-507-B-6	1/2	3/8	Ball	6	152
EX-622	5/8	3/8	Pin	1 1/2	38
EX-750	3/4	3/8	7/32 Drill Hole	1 1/2	38
EX-750-B	3/4	3/8	Ball	1 1/2	38

3/8" Square Drive Universal Adapters

Male Square to Female Square



Universal wrenches must not be used with impact drivers. Maximum operating angle is 30°.

Part Number	Male Square In.	Female Square In.	Type of Lock	Overall Length		Largest Diameter	
				In.	mm	In.	mm
MF-27	1/4	3/8	Pin	1 5/16	49	3/4	19
MF-27B	1/4	3/8	Ball	1 5/16	49	3/4	19
MF-37	3/8	3/8	Pin	2 1/8	54	3/4	19
MF-37B	3/8	3/8	Ball	2 1/8	54	3/4	19
MF-38	3/8	3/8	Pin	2 1/2	64	7/8	22
MF-38B	3/8	3/8	Ball	2 1/2	64	7/8	22

3/8" Square Drive Universal Adapters - Extension

Male Square to Female Square



(Standard Type Shown)

Standard lengths are 3", 6", 9" and 12" (76, 152, 229 and 305mm)

Standard	Part Number	Male Square In.	Female Square In.	Type of Lock	Largest Diameter		
	Tension				In.	mm	
	KAM-25-3	KDM-25-3	1/4	3/8	Pin	5/8	16
	KAM-37-3	KDM-37-3	3/8	3/8	Pin	3/4	19
	-	KDM-37-6	3/8	3/8	Pin	3/4	19
	KAM-37-B-3	KDM-37-B-3	3/8	3/8	Ball	3/4	19
	KAM-38-6	KDM-38-6	3/8	3/8	Pin	7/8	22