

ATX™ JBES and ECES Series 316L Stainless Steel Enclosure Accessories

Increased Safety

ATEX/IECEX:
Zone 1 and 2 - 21 and 22
II 2 GD
IP66 - IK10

Mounting Accessories - Continued

	Enclosure Dimensions mm (in)		Mounting Pan Dimensions mm (in)	Catalog Number
	Height	Width		
Mounting Pan – Zinc Plated Steel				
	120 (4.72)	120 (4.72)	100 x 100 (3.93 x 3.93)	097277
	120 (4.72)	180 (7.09)	100 x 160 (3.93 x 6.30)	097278
	180 (7.09)	180 (7.09)	160 x 160 (6.30 x 6.30)	097279
	220 (8.66)	260 (10.24)	160 x 200 (6.30 x 7.87)	097280
	220 (8.66)	370 (14.57)	160 x 310 (6.30 x 12.20)	097281
	260 (10.24)	370 (14.57)	200 x 310 (7.87 x 12.20)	097282
	370 (14.57)	370 (14.57)	310 x 310 (12.20 x 21.20)	097283
	370 (14.57)	560 (22.05)	310 x 500 (12.20 x 19.68)	097284
	370 (14.57)	750 (29.53)	310 x 690 (12.20 x 27.17)	097285
	560 (22.05)	560 (22.05)	500 x 500 (19.68 x 19.68)	097286
	560 (22.05)	750 (29.53)	500 x 690 (19.68 x 27.17)	097287
	1130 (44.49)	750 (29.53)	690 x 1070 (27.17 x 42.13)	097288
	Spacers for Mounting at Back of Box <i>Set of two insulated pillars for copper bar 12 x 4 mm (0.47 x 0.16").</i>			
	Height = 100 mm (3.94")			097206
	Height = 50 mm (1.97")			097207
	Conversion Kit – Door to Cover <i>Must be used to remove hinges.</i>			097202
	Spare Hinges Set of Two			097201
	Spare Mounting Brackets – Set of Two One left and one right.			097200
	Self Adhesive Pocket for Drawings			
	External dimensions: 260 x 165 mm (10.24 x 6.50") Internal dimensions: 230 x 130 x 18 mm (9.06 x 5.12 x .071")			097263
	External dimensions: 340 x 235 mm (13.39 x 9.25") Internal dimensions: 310 x 200 x 18 mm (12.20 x 7.87 x 0.71")			097264
	Additional Door Padlocking Device Padlock not supplied.			097209
	Locking Bracket Locks door in open position during wiring			097265

Appleton®

ENCLOSURES AND JUNCTION BOXES: ATEX/IECEX INCREASED SAFETY JUNCTION BOXES