

W Series Cast Junction Box Options

Boxes Available for Raintight, Watertight, or Submersible Applications

ENCLOSURES AND JUNCTION BOXES: ORDINARY LOCATION JUNCTION BOXES

Drilling and Tapping

Applies to: Types WYS, WYL, WYF, WYW-T, WYT, WYC, WYU, WYR.

Conduit Size Inches	Catalog Number			
	Drilling Only Slip Hole	Drilling & Tapping No Boss	Boss Only 5 Threads without Hole	Boss for 4 Threads and Tapping
3/8	ASH-38	ADT-38	ABWH-38	ABDT-38
1/2	ASH-50	ADT-50	ABWH-50	ABDT-50
3/4	ASH-75	ADT-75	ABWH-75	ABDT-75
1	ASH-100	ADT-100	ABWH-100	ABDT-100
1-1/4	ASH-125	ADT-125	ABWH-125	ABDT-125
1-1/2	ASH-150	ADT-150	ABWH-150	ABDT-150
2	ASH-200	ADT-200	ABWH-200	ABDT-200
2-1/2	ASH-250	ADT-250	ABWH-250	ABDT-250
3	ASH-300	ADT-300	ABWH-300	ABDT-300
3-1/2	ASH-350	ADT-350	ABWH-350	ABDT-350
4	ASH-400	ADT-400	ABWH-400	ABDT-400
4-1/2	ASH-450	ADT-450	ABWH-450	ABDT-450
5	ASH-500	ADT-500	ABWH-500	ABDT-500
6	ASH-600	ADT-600	ABWH-600	ABDT-600

Combination Drain and Breather Fittings

D and T and installation included.

Size (Inches)	Catalog Number
3/8	AMDB-38
1/2	AMDB-50

Interior Mounting Buttons

Quantity Per Box	Catalog Number
1	A1-MBT
2	A2-MBT
3	A3-MBT
4	A4-MBT

Grounding Kits

Wire Capacity Al-Cu Tinned Copper	Catalog Number
#14-4 AWG	AGK-04
8-1/0 AWG	AGK-10
6 AWG-250kcmil	AGK-25

Hinges

Type	Box Size in Inches/Millimeters	Number of Hinges Per Set	Catalog Number
Stainless Steel	Up to 12 x 12/304.8 x 304.8	2	AHNG-22SS
Butt Type	Up to 18 x 18/457.2 x 457.2	2	AHNG-23SS
For WYU Boxes	Larger than 18 x 18/457.2 x 457.2	3	AHNG-33SS

Hasps

Hot dip galvanized steel (lock not Included).

Box Size in Inches/Millimeters	Catalog Number
Up to 12" x 12" / 304.8 x 304.8	AHSP-13SG
Larger than 12" x 12" / 304.8 x 304.8	AHSP-15SG

Letters Engraved on Box Covers

Description	Catalog Number	
	Engraved	Raised
Up to 10 letters, one line	AENGRAVE-1	ARAISED-1
Up to 20 letters, two lines	AENGRAVE-2	ARAISED-2

Optional Mounting Lugs with Bolt Holes†

Maximum Box Size — L x W in in/mm	No. of Lugs	Catalog Number
Sizes up to 6" x 4" / 152.4 x 101.6	2	A2-ML-0604
	4	A4-ML-0604
Sizes 6" x 6" to 12" x 4" / 152.4 x 152.4 up to 304.8 x 101.6	2	A2-ML-1204
	4	A4-ML-1204
Sizes 12" x 6" up to 18" x 16" / 304.8 x 152.4 up to 457.2 x 406.4	2	A2-ML-1816
	4	A4-ML-1816
Sizes 18" x 18" and larger / 457.2 x 457.2 and larger	4	A4-ML-3636

† Mounting lugs are standard equipment on surface mounted boxes over 100 in³/1.6 dm³ of internal volume at no additional charge.