

# FS and FD Cast Hub Device Boxes

UNILETS™ for use with Threaded Rigid Metal Conduit and IMC. Furnished with Internal Ground Screw.

NEC:  
Listed for Ordinary Locations

FS Box (Shallow) 2.00" deep, FD Box (Deep) 2.69" deep, ED (Extra Deep) 3.06" deep

|   | Type | Depth          | Hub Size (Inches) | Catalog Number           |                    |
|---|------|----------------|-------------------|--------------------------|--------------------|
|   |      |                |                   | Malleable Iron Ridge Top | Aluminum Ridge Top |
|    | FS   | Shallow        | 1/2               | FS-2-50                  | FS-2-50-A          |
|   |      |                | 3/4               | FS-2-75                  | FS-2-75-A          |
|   |      |                | 1                 | FS-2-100                 | —                  |
|   | FD   | Deep           | 1/2               | FD-2-50                  | —                  |
|   |      |                | 1/2               | FD-2-50ED                | —                  |
|   |      |                | 3/4               | FD-2-75                  | FD-2-75-A          |
|   |      |                | 3/4               | FD-2-75ED                | —                  |
|   |      | 1              | FD-2-100          | —                        |                    |
|   |      | 1              | FD-2-100ED        | —                        |                    |
|  | FSC  | Shallow        | 1/2               | FSC-2-50                 | —                  |
|   |      |                | 3/4               | FSC-2-75                 | FSC-2-75-A         |
|   |      |                | 1                 | FSC-2-100                | —                  |
|   | FDC  | Deep           | 1/2               | FDC-2-50                 | —                  |
|   |      |                | 1/2               | FDC-2-50ED               | —                  |
|   |      |                | 3/4               | FDC-2-75                 | FDC-2-75-A         |
|   |      |                | 3/4               | FDC-2-75ED               | —                  |
|   |      | 1              | FDC-2-100         | —                        |                    |
|   |      | 1              | FDC-2-100ED       | —                        |                    |
|  | FSS  | Shallow        | 1/2               | FSS-2-50                 | —                  |
|   |      |                | 3/4               | FSS-2-75                 | FSS-2-75-A         |
|   |      |                | 1                 | FSS-2-100                | —                  |
|   | FDS  | Deep           | 3/4               | FDS-2-75                 | —                  |
|  | FSD  | Shallow ①      | 1/2-3/4           | FSD-2-75                 | —                  |
|  | FS   | 1" Extension ② | —                 | FS-2EXT                  | —                  |

① Largest hub at bottom in illustration.

② Extension does not have a ground screw.

Shaded boxes include mounting feet (feet not shown for boxes on this page).