

## Quartzlite™ Floodlights

For 300W thru 1500W quartz tungsten halogen lamps.







### Ordering Information

(Illumination based on use of T-3 Quartz tungsten Halogen lamps)

Description	NEMA Type	Beam Spread		Lumens	Candlepower		Catalog Number		
		Horiz.	Vert.		Max.	Avg. Max.	With Lamp	Without Lamp	
<b>Quartzlite™ 1500</b>									
Wide Beam	6 x 6	128.0°	103.0°	23,218	18,689	17,564	G-1500L240 ❶ G-1500L277 ❷	G-1500-❸ —	
<b>Quartzlite™ 500</b>									
Wide	5 x 5	95°	92°	6,846	8,416	7,685	G-500-5-L130 ❹	G-500-5 ❺	

- ❶ Furnished with 1500W lamps for 240-volt line operation. ❷ Furnished with 1500W lamps for 277-volt line operation. ❸ For 1500W lamps for 208, 220, 240 or 277-volt line operation; 1250W lamps for 208-volt line operation; 1000W lamps for 220 or 240-volt line operation.  
❹ Furnished with 500W lamps for 120 or 130-volt line operation. ❺ For 300W or 500W lamps for 120 or 130-volt line operation.

### Mounting Fittings and Accessories

Dimensions	Description	Cat. No.	Dimensions	Description	Cat. No.
	<b>Crossarm Mount and Wiring Compartment</b> 180° horizontal position scale, mounts with bolt (not furnished). Aluminum with architectural bronze POLYESTER finish. Includes cord grip.	G-6028N		<b>Channel Crossarm</b> Extruded aluminum, with slide-off cover. Has six 3/4" threaded holes, with three close-up plugs. Mounts five 500W or four 1500W Quartzlites. Mounts on 3/4" conduit or G-810 poletop fitter.	G-6017
	<b>Pipe or Wall Mount Bracket</b> Mounts on 1" to 2" pipe, vertical or horizontal, or mounts on flat surfaces (used with G-6028N). Includes U-bolts and bolt for G-6028N. Malleable iron, zinc plated, chromate sealed, architectural bronze POLYESTER finish.	G-VB101		<b>Poletop Fitter</b> Cast aluminum, for mounting to 1-1/2" or 2" pipe. Has setscrews for securing to pole, 3/4" tapped top hub to accommodate Quartzlite or Channel Crossarm above. Architectural bronze POLYESTER finish.	G-810
	<b>Top Visor</b> 500W	GMM4V		<b>Replacement Lens</b> 500W 1500W	601252002 601252001
	<b>Wire Guard</b> 500W	G-506	<b>Replacement Lens Frame Assembly</b> (Complete with Lens) 500W 1500W	<b>Replacement Lens Frame Assembly</b> (Complete with Lens) 500W 1500W	G5005RFL G1500RFL
			<b>Replacement Socket Assembly (Pair)</b> 500W 1500W	<b>Replacement Socket Assembly (Pair)</b> 500W 1500W	G5005RS G1500RS