


Accessories and Parts for Code•Master Jr.™ PL Lighting Fixtures

	Description	Catalog Number															
 <p data-bbox="204 653 367 674">Standard Dome</p> <p data-bbox="472 653 574 674">30° Angle</p>	<p data-bbox="643 459 846 485">Polyester Reflectors</p> <p data-bbox="643 487 1000 512">Furnished with stainless steel screws</p> <p data-bbox="643 527 805 575">Standard Dome 30° Angle</p>	<p data-bbox="1312 527 1398 552">KR2-ST</p> <p data-bbox="1312 554 1398 575">KR2-AN</p>															
	<p data-bbox="643 732 829 758">Three-Way Exit Sign</p> <p data-bbox="643 760 1081 785">Epoxy enameled steel — 6"-high red lettering</p> <p data-bbox="643 787 1049 837">Mounts to Code•Master Jr. PL fixture units in place of guard.</p>	<p data-bbox="1312 753 1406 774">CJEXRN</p>															
	<p data-bbox="643 905 846 930">Single Sided Exit Sign</p> <p data-bbox="643 932 1081 957">Epoxy enameled steel — 6"-high red lettering</p> <p data-bbox="643 959 1049 1010">Mounts to Code•Master Jr. PL fixture units in place of guard.</p>	<p data-bbox="1312 926 1422 947">AEXR-15R</p>															
	<p data-bbox="643 1058 862 1110">Prismatic Glass Globe and Ring Assembly</p>	<p data-bbox="1312 1131 1422 1152">CJGL-175</p>															
	<p data-bbox="643 1236 821 1257">Aluminum Guards</p>	<p data-bbox="1312 1283 1406 1304">CJGU-15</p>															
	<p data-bbox="643 1415 1097 1436">Replacement Parts— 22W, 28W, 44W and 56W</p>	<table border="0"> <tr> <td data-bbox="643 1457 846 1482">Socket (lampholder)</td> <td data-bbox="1049 1457 1243 1509">22 watt (GX32D-2) 28 watt (GX32D-3)</td> <td data-bbox="1312 1457 1382 1509">CJS22 CJS28</td> </tr> <tr> <td data-bbox="643 1535 902 1560">Socket Bracket Assembly</td> <td data-bbox="1049 1535 1130 1629">22 watt 28 watt 44 watt 56 watt</td> <td data-bbox="1312 1535 1398 1629">CJSA22 CJSA28 CJSA44 CJSA56</td> </tr> <tr> <td data-bbox="643 1661 708 1686">Lamps</td> <td data-bbox="1049 1661 1130 1713">22 watt 28 watt</td> <td data-bbox="1312 1661 1382 1713">PLC22 PLC28</td> </tr> <tr> <td data-bbox="643 1734 854 1759">Replacement Ballast</td> <td data-bbox="1049 1734 1130 1787">22 watt 28 watt</td> <td data-bbox="1312 1734 1455 1787">59661250005 59661250006</td> </tr> <tr> <td data-bbox="643 1808 911 1860">Connection Block For all Code•Master fixtures</td> <td></td> <td data-bbox="1312 1839 1373 1860">VPT-7</td> </tr> </table>	Socket (lampholder)	22 watt (GX32D-2) 28 watt (GX32D-3)	CJS22 CJS28	Socket Bracket Assembly	22 watt 28 watt 44 watt 56 watt	CJSA22 CJSA28 CJSA44 CJSA56	Lamps	22 watt 28 watt	PLC22 PLC28	Replacement Ballast	22 watt 28 watt	59661250005 59661250006	Connection Block For all Code•Master fixtures		VPT-7
Socket (lampholder)	22 watt (GX32D-2) 28 watt (GX32D-3)	CJS22 CJS28															
Socket Bracket Assembly	22 watt 28 watt 44 watt 56 watt	CJSA22 CJSA28 CJSA44 CJSA56															
Lamps	22 watt 28 watt	PLC22 PLC28															
Replacement Ballast	22 watt 28 watt	59661250005 59661250006															
Connection Block For all Code•Master fixtures		VPT-7															