


# UniCode™ Series Factory Sealed Control Stations and Pilot Lights

**NEC/CEC:**  
 Class I, Division 2, Groups B, C, D  
 Class I, Zone 2, Group IIC  
 Class II, Groups E, F, G  
 Class III

**NEC/CEC:**  
 Type 3, 3R, 4, 4X  
 IP66

## Catalog Numbering Guide



Device Descriptions	Device Code
Momentary Push Button - 1NO/NC	U1 ①
Momentary Push Button - 2NO/NC	UD1
Maintained Push Button - 1NO/NC	UM1
Maintained Push Button - 2NO/NC	UDM1
Pilot Light	J1 ②
2-POS 2-CKT Selector Switch	12
3-POS 2-CKT Selector Switch	102
2-POS 4-CKT Selector Switch	35
3-POS 4-CKT Selector Switch (Labyrinth Switch Only)	345
Close-up Plug	PLG
Options Descriptions	Device Code
Amber Pilot Light	JGBA
Green Pilot Light	JGBG
Blue Pilot Light	JGBB
DC Rating for Pilot Light	DC
Red Mushroom Head - Momentary Push Button	NMRBRE
Green Mushroom Head - Momentary Push Button	NMRBGR
Black Mushroom Head - Momentary Push Button	NMRBBL
Black Mushroom Head - Maintained Push Button	NMRBMBL
Green Mushroom Head - Maintained Push Button	NMRBMGR
Spring Return from Right - Selector Switch (3 Position Only)	SRC
Spring Return from Left - Selector Switch (3 Position Only)	SLC
Spring Return from Right and Left - Selector Switch (3 Pos, 4 Ckt and Alt Contacts Only)	SRL
Alternate Contacts - Selector Switch	ALT
Red Momentary Push Button	PBRE
Green Momentary Push Button	PBGR
Accessories Descriptions	Accessory Code
Stainless Steel Mounting Feet	SSMTG
Mushroom Head Push Button Locking Guard	UCMPBLG

① Momentary push buttons are black. Add —**PBRE** for red or —**PBGR** for green.  
 ② Pilot lights are red. Add —**JGBA** for amber, —**JGBG** for green or —**JGBB** for blue.

# UniCode™ Series Factory Sealed Control Stations and Pilot Lights

NEC/CEC:  
Class I, Division 2, Groups B, C, D  
Class I, Zone 2, Group IIC  
Class II, Groups E, F, G  
Class III

NEC/CEC:  
Type 3, 3R, 4, 4X  
IP66

Hub Size (Inches)		Description	Diagram	Standard Legend Plate Marking and Device Color	Catalog Number	
					Dead-End	Feed-Thru
<b>Push Buttons</b>						
<b>Momentary Contact</b>						
	1/2	1 Circuit Universal		Start/Green	UCS150U1	UCSC150U1
	3/4				UCS175U1	UCSC175U1
	1				UCS110U1	UCSC110U1
	1/2	2 Circuits Universal		Start/Green Stop/Red	UCS250U2	UCSC250U2
	3/4				UCS275U2	UCSC275U2
	1				UCS210U2	UCSC210U2
	1/2	3 Circuits Universal		Blank/Black	UCS350U3	UCSC350U3
	3/4				UCS375U3	UCSC375U3
	1				UCS310U3	UCSC310U3
	1/2	4 Circuits Universal		Blank/Black	UCS450U4	UCSC450U4
	3/4				UCS475U4	UCSC475U4
	1				UCS410U4	UCSC410U4
<b>Maintained Contact</b>						
1/2	1 Circuit Universal		Emergency Stop/Red	UCS150UM1	UCSC150UM1	
3/4				UCS175UM1	UCSC175UM1	
1				UCS110UM1	UCSC110UM1	
<b>Pilot Lights</b>						
<b>Pilot Light has terminals for 120 or 240 Vac – Uses 8 cluster LED</b>						
	1/2	1 Pilot Light		Blank/Red	UCS150J1	UCSC150J1
	3/4				UCS175J1	UCSC175J1
	1				UCS110J1	UCSC110J1
	1/2	2 Pilot Lights		Blank/Red	UCS250J2	UCSC250J2
	3/4				UCS275J2	UCSC275J2
	1				UCS210J2	UCSC210J2
	1/2	3 Pilot Lights		Blank/Red	UCS350J3	UCSC350J3
	3/4				UCS375J3	UCSC375J3
	1				UCS310J3	UCSC310J3
	1/2	4 Pilot Lights		Blank/Red	UCS450J4	UCSC450J4
	3/4				UCS475J4	UCSC475J4
	1				UCS410J4	UCSC410J4

APPLETON™

CONTROLS: NEC/CEC EXPLOSIONPROOF CONTROL STATIONS AND SWITCHES

# UniCode™ Series Factory Sealed Control Stations and Pilot Lights

NEC/CEC:  
Class I, Division 2, Groups B, C, D  
Class I, Zone 2, Group IIC  
Class II, Groups E, F, G  
Class III

NEC/CEC:  
Type 3, 3R, 4, 4X  
IP66

APPLETON™

CONTROLS: NEC/CEC EXPLOSIONPROOF CONTROL STATIONS AND SWITCHES

Hub Size (Inches)	Description	Diagram			Standard Legend Plate Marking and Device Color	Catalog Number		
		Left	Center	Right		Dead-End	Feed-Thru	
<b>Selector Switches</b>								
1/2	2 Positions, 2 Circuits		None		On/Off	UCS15012	UCSC15012	
3/4						UCS17512	UCSC17512	
1						UCS11012	UCSC11012	
1/2	2 Positions, 4 Circuits		None		On/Off	UCS15035	UCSC15035	
3/4						UCS17535	UCSC17535	
1						UCS11035	UCSC11035	
1/2	3 Positions, 2 Circuits				Hand/Off/Auto	UCS150102	UCSC150102	
3/4						UCS175102	UCSC175102	
1						UCS110102	UCSC110102	
1/2	3 Positions, 4 Circuits				Hand/Off/Auto	UCS150345	UCSC150345	
3/4						UCS175345	UCSC175345	
1						UCS110345	UCSC110345	
1/2	3 Positions, 4 Circuits, Alternate Contacts				Hand/Off/Auto	UCS150345ALT	UCSC150345ALT	
3/4						UCS175345ALT	UCSC175345ALT	
1						UCS110345ALT	UCSC110345ALT	
<b>Pilot Lights and Push Buttons</b>								
1/2	1 Circuit Universal and 1 Pilot Light				Pilots: Blank/Red; Push Button: Start/Green	UCS250J1U1	UCSC250J1U1	
3/4						UCS275J1U1	UCSC275J1U1	
1						UCS210J1U1	UCSC210J1U1	
1/2	1 Circuit Universal and 2 Pilot Lights				Pilots: Blank/Red; Push Button: Start/Green	UCS350J2U1	UCSC350J2U1	
3/4						UCS375J2U1	UCSC375J2U1	
1						UCS310J2U1	UCSC310J2U1	
1/2	2 Circuits Universal and 1 Pilot Light				Pilot: Blank/Red; Push Button: Start/Green, Stop/Red	UCS350J1U2	UCSC350J1U2	
3/4						UCS375J1U2	UCSC375J1U2	
1						UCS310J1U2	UCSC310J1U2	
1/2	2 Circuits Universal and 2 Pilot Lights				Pilot: Blank/Red; Push Button: Start/Green, Stop/Red	UCS450J2U2	UCSC450J2U2	
3/4						UCS475J2U2	UCSC475J2U2	
1						UCS410J2U2	UCSC410J2U2	
<b>Pilot Lights, Push Buttons and Selector Switches</b>								
1/2	1 Circuit Universal, 1 Pilot Light and 1 Selector Switch			None		Pilot: Blank/Red; Push Button: Blank/Black; Sel. Switch: On/Off	UCS350J1U112	UCSC350J1U112
3/4							UCS375J1U112	UCSC375J1U112
1							UCS310J1U112	UCSC310J1U112
1/2	1 Circuit Universal, 1 Pilot Light and 1 Selector Switch					Pilot: Blank/Red; Push Button: Blank/Black; Sel. Switch: Hand/On/Off	UCS350J1U1102	UCSC350J1U1102
3/4							UCS375J1U1102	UCSC375J1U1102
1							UCS310J1U1102	UCSC310J1U1102