

▲ Class I, Div. 2,  
Groups A, B, C, D;  
Class II, Div. 1 and 2,  
Groups E, F, G; ■  
Class III ■  
CSA Encl. 3

## V and VH Incandescent Lighting Fixtures: Enclosed and Gasketed

60 thru 300W Incandescent Lamps.  
For use with Threaded Rigid Metal Conduit and IMC.

	Lamp	Size (Inches)	Catalogue Number	
			Less Guard	With Guard
	<b>Pendant</b>			
	Flexible or Rigid Mounting			
	60-150W, A-21	1/2	VA160	VA160G
		3/4	VA260	VA260G
	150-300W, PS-25	1/2	VHA1700	VHA1700G
		3/4	VHA2700	VHA2700G
	<b>Ceiling - with Junction Box</b>			
	<b>Four Entry "X"</b>			
	60-150W, A-23	1/2	VGPX160	VGPX160G
		3/4	VGPX260	VGPX260G
	150-300W, PS-25	1/2	VHGPX1700	VHGPX1700G
		3/4	VHGPX2700	VHGPX2700G
	<b>Brass Construction</b>			
	60-150W, A-21	3/4	VBGPX260	VBGPX260G
	150-300W, PS-25	3/4	VHBGPX2700	VHBGPX2700G
	<b>Wall - with Junction Box</b>			
	<b>Four Entry "X"</b>			
	60-150W, A-23	1/2	VGSX160	VGSX160G
	3/4	VGSX260	VGSX260G	
	150-300W, PS-25	1/2	VHGSX1700	VHGSX1700G
		3/4	VHGSX2700	VHGSX2700G
	<b>Brass Construction</b>			
	60-150W, A-21	3/4	VBGSX260	VBGSX260G
	150-300W, PS-25	3/4	VHBGSX2700	VHBGSX2700G

All fixtures supplied with 3/4" Entry Hubs and 1/2" Reducers.

■ 300W PS-25 not approved for Class II, Div. 1 and 2, Group G; Class III

## Component Parts Listings: V and VH Series.

Fixtures Complete with Globe and Guard.\*

Catalogue Number Ordered*	Hub (Inches)	Mounting Hood	Globe	Guard		
<b>V and VH Series</b>						
<b>Pendant</b>						
VA160-G	1/2	VA140	VGL1CL	V680		
VA260-G	3/4	VA240	VGL1CL	V680		
VHA1700-G	1/2	VHA1400	VH700	VH720		
VHA2700-G	3/4	VHA2400	VH700	VH720		
<b>Ceiling - with Junction Box</b>						
VGPX160-G	1/2	VGPX140	VGL1CL	V680	<b>X</b>	Four Entry
VGPX260-G	3/4	VGPX240	VGL1CL	V680		
VHGPX1700-G	1/2	VHGPX1400	VH700	VH720		
VHGPX2700-G	3/4	VHGPX2400	VH700	VH720		
<b>Ceiling - with Cast Hubs</b>						
V□160-G	1/2	V□140	VGL1CL	V680		
V□260-G	3/4	V□240	VGL1CL	V680		
VH□1700-G	1/2	VH□1400	VH700	VH720		
VH□2700-G	3/4	VH□2400	VH700	VH720		
<input type="checkbox"/> To order tapped entries insert designation: - Dead End "E" (no designation) C Feed Thru L Right Angle T Three Entry X Four Entry						
<b>Wall - with Junction Box</b>						
VGSX160-G	1/2	VGSX140	VGL1CL	V680	<b>X</b>	Four Entry
VGSX260-G	3/4	VGSX240	VGL1CL	V680		
VHGSX1700-G	1/2	VHGSX1400	VH700	VH720		
VHGSX2700-G	3/4	VHGSX2400	VH700	VH720		

\* To order fixtures without guard – delete suffix "G"