


MANIFOLD FLANGE CONNECTIONS



MANIFOLD FLANGE CONNECTIONS SAVE YOU TIME AND MONEY WHILE AVOIDING THE INSTALLATION HEADACHES OF THREADED PIPE

FLANGE CONNECTIONS FOR EVERY PRODUCT



NO THREADS. NO SWEAT.

» GET RIGHT TO THE SOURCE

With Banjo manifold flange connections, the days of spending hours unhooking entire systems of valves and fittings are over. You can directly isolate and replace the problematic part or replumb sections without disassembling the whole system.

⚡ SKIP THE TAPE AND SEALANT

Flange connections utilize clamps instead of threads, facilitating quick and easy assembly and disassembly while ensuring a leak-proof system. Threaded pipe needs tape or sealant, and the slightest imperfection in the pipe or seal can cause a leak. With properly installed flange connections, you won't worry about connection leaks or wait for sealant to cure.

⌚ SAVE TIME. SAVE MONEY.

Time spent unthreading systems and repairing leaks from faulty connections is unproductive and ultimately hits your pocketbook. Banjo's manifold flange systems get you back in the field and out of the shop in no time.

MANIFOLD FLANGE CONNECTION ASSEMBLY

Clamps and gaskets make a quick, easy and secure seal.

WHAT OUR CUSTOMERS SAY

“ Banjo's biggest **innovation** was when they came out with the flange fittings... it's just light years ahead of where we were before. **Eliminating leaks** and being able to **reconfigure** things is so easy. ”

- **Chad Middlemas**, Domestic Sales Manager
Hagie

“ With a threaded system, I have to start at one end or the other and take parts apart until I get to the piece I need. As you can imagine, **it takes a lot more time to mess with the threaded parts.** ”

- **JD England**, Product Support
Equipment Technologies

C O N N E C T W I T H C O N F I D E N C E™



MANIFOLD FLANGE CONNECTIONS OFFER A VARIETY OF CHEMICAL RESISTANCE, SIZING, AND DURABILITY OPTIONS THAT SUPPORT YOUR BUDGET

MANIFOLD MODEL CHART

	MANIFOLD MODELS			
	M100 SERIES 1" FULL PORT	M200 SERIES 2" STANDARD PORT	M220 SERIES 2" FULL PORT	M300 SERIES 3" FULL PORT
BANJO PRODUCTS ELECTRIC VALVES	✓	✓	✓	✓
LEV SERIES ELECTRIC VALVES	✓	X	X	X
3-WAY ELECTRIC VALVES	✓	✓	✓	✓
BOLTED VALVES	✓	✓	✓	✓
POLYPROPYLENE STUBBY VALVES	X	✓	✓	✓
STAINLESS STEEL STUBBY VALVES	X	X	✓	✓
3-WAY BOLTED VALVES	✓	✓	✓	✓
POLYPROPYLENE DRY-MATES™	X	✓	✓	✓
INDUCTOR SYSTEMS	X	X	✓	✓
SWEEPS	✓	✓	✓	✓
PUMPS	X	X	✓	✓
FLOW METERS	✓	X	✓	✓
BOOM NOZZLES	✓	X	X	X
CHECK VALVES	✓	✓	✓	✓
FITTINGS	✓	✓	✓	✓
LINE STRAINERS	✓	✓	✓	✓
TANK FITTINGS	✓	✓	✓	✓




BANJO CORPORATION
 A Unit of IDEX Corporation
 150 Banjo Drive
 Crawfordsville, IN 47933 U.S.A.
 Telephone: (765) 362-7367
 Fax: (765) 362-0744
banjocorp.com

Watch this video for more information about the benefits of Manifold Flange Connections by scanning this QR code or visit:



BanjoCorp.com/Fluid-Handling-Training





PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	SW10	#10 WASHER
2	1	V07020	#10-24x0.50 HHCS 18-8SS
3	1	V10060	THRUST BEARING
4	4	V10117	5/16 - 18 X 3 1/2" HHCS
5	4	V10118	5/16" LOCKWASHER
6	4	V10119	5/16"-18 SS NUT
7	1	V10151	1" VALVE STEM W/ INSERT
8	1	V10155	VALVE BALL 1" FP, TUMBLED
9	1	V10159	UPPER-LOWER STEM BUSHING, PTFE
10	1	V10163	AS568A -113 O-RING, FKM, BROWN
11	1	V10254	1" VALVE BODY
12	2	V10258A	1" BALL VALVE SEAT, STYLE A
13	2	V10264	AS568A -036 O-RING, FKM, BROWN
14	2	V10278	1" MANIFOLD ENDPLATE, MACHINED
15	1	V10353T	BOTTOM LOAD T-HANDLE
16	1	V20353C	1 1/8" CAPLUG



THIS DRAWING AND ALL INFORMATION CONTAINED THEREON ARE THE EXCLUSIVE PROPERTY OF BANJO CORPORATION.

UNLESS SPECIFICALLY NOTED, THIS DRAWING AND ITEMS SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE AT ANY TIME.



BANJO CORPORATION
 A UNIT OF IDEX CORPORATION
 150 BANJO DRIVE, CRAWFORDSVILLE, IN 47933
 WEB SITE: WWW.BANJOCORP.COM
 E-MAIL: BANJOSALES@IDEXCORP.COM

DESCRIPTION: 1" FP MANIFOLD FLANGED VALVE	PART NUMBER: MVT100CF
---	---------------------------------