



Assembly Specs:
 Body bolt tightening torque: 75 in-lb
 Max stem turning torque: 75 in-lb



REPLACEMENT PARTS EV204FP-EVR204FP				
ITEM	PART NO	DESCRIPTION	QTY	PRICE
1	EV204XR1	2" Full Port Electric Valve Sub Assembly	1	\$298.37
2	MVE004	Electric Valve Flange Gasket	1	\$0.39
3	FC100	1" Flange Clamp	1	\$9.61
4	EV4100	1 1/4 Second 3 Wire Motor Assembly	1	\$405.73
4	EVR4100	Regulating 4 Wire, 4 Second	1	\$304.30
4	EVR4102	Regulating 2 Wire, 6 Second	1	\$304.30
5	VE25356A	2" Full Port Threaded End Plate	2	\$18.59
6	V20019	3/8" 16 SS Hex Nut	4	\$1.00
7	VE25255SSH	2" 316 SS Hollow Ball	1	\$51.57
8	V20018	3/8" SS Lock Washer	4	\$0.41
9	MEV25151	1" SS Stem w/Seals	1	\$66.20
10	VE25258A	1 1/2" & 2" Electric Ball Seat	2	\$10.13
11	MEV25254A	1 1/2" & 2" Body	1	\$19.65
12	V25264	2" FKM (viton type) Body O-Ring	2	\$9.52

REPLACEMENT PARTS EV204FP-EVR204FP				
ITEM	PART NO	DESCRIPTION	QTY	PRICE
13	V25017	3/8" x 4" SS Body Bolt	4	\$2.29
14	VE15220	Housing Screw	6	\$0.27
15	MVE25102	Housing Top for Large Motor	1	\$39.14
16	VE4987	1 1/4 Second Hi Torque On/Off Motor	1	\$384.35
16	VE4988	4 Second 12 Volt Wire High Torque Motor	1	\$373.14
17	MVE107	Motor Shaft Gasket	1	\$0.39
18	MVE002	Heyco 1/4" Threaded Bushing	1	\$0.80
19	MVE104	Outer Housing Gasket	1	\$2.93
20	VE109E	Indicator Seal	1	\$4.45
21	MVE007	3mm x 5mm FKM (viton type) O-Ring	1	\$1.00
22	MVE106	Inner Housing Gasket	1	\$2.59
23	VE107A	Flow Indicator	1	\$6.99
24	MEV25101	Housing Bottom for Large Motor	1	\$53.81
25	EV25210	Repair Kit (Includes items 2, 9, 10, 12)	1	\$95.69