

## Polyester Labels for Inside Panel Markings and General ID (B-423, B-430 and B-488)

High performance white or clear polyester material that is best for use on smooth, flat surfaces

- B-488 polyester is a solvent-resistant material
- B-499 nylon cloth or B-595 (vinyl label materials are recommended if surface is highly textured)



Figure 33b



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll	Ribbon in Cartridge
<b>B-423 Polyester (gloss white)</b>								
Fig. 33b	* M21-250-423	B-423	Polyester	Black on White	0.250 (6.35)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-375-423	B-423	Polyester	Black on White	0.375 (9.53)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-500-423	B-423	Polyester	Black on White	0.500 (12.70)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-750-423	B-423	Polyester	Black on White	0.750 (19.05)	21 ft (6.40 m)	1 roll (cont.)	R6200
<b>B-430 Polyester (clear)</b>								
Fig. 33b	* M21-250-430	B-430	Polyester	Black on Clear	0.250 (6.35)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-375-430	B-430	Polyester	Black on Clear	0.375 (9.53)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-500-430	B-430	Polyester	Black on Clear	0.500 (12.70)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-750-430	B-430	Polyester	Black on Clear	0.750 (19.05)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	* M21-250-430-WT-CL	B-430	Polyester	White on Clear	0.250 (6.35)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-375-430-WT-CL	B-430	Polyester	White on Clear	0.375 (9.53)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-500-430-WT-CL	B-430	Polyester	White on Clear	0.500 (12.70)	21 ft (6.40 m)	1 roll (cont.)	R6200
Fig. 33b	M21-750-430-WT-CL	B-430	Polyester	White on Clear	0.750 (19.05)	21 ft (6.40 m)	1 roll (cont.)	R6200
<b>B-488 Polyester (matte white)</b>								
Fig. 33b	M21-375-488	B-488	Polyester	Black on White	0.375 (9.53)	21 ft (6.40 m)	1 roll (cont.)	R4300
Fig. 33b	M21-500-488	B-488	Polyester	Black on White	0.500 (12.70)	21 ft (6.40 m)	1 roll (cont.)	R4300
Fig. 33b	M21-750-488	B-488	Polyester	Black on White	0.750 (19.05)	21 ft (6.40 m)	1 roll (cont.)	R4300

\* Cartridge is only compatible with the BMP®21-PLUS printer.

## Laboratory Labels (B-461 and B-7425)

- B-461 features clear, wrap-around tail that overlaminates white print-on area to protect text
- B-7425 economical white polypropylene is chemical and high-temperature resistant



Figure 33b



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll	Ribbon in Cartridge
<b>B-461 Self-Laminating Polyester</b>								
Fig. 33b	M21-375-461	B-461	Polyester	Black on White	0.375 (9.53)	21 ft (6.40 m)	1 roll (cont.)	R4300
Fig. 33b	M21-500-461	B-461	Polyester	Black on White	0.500 (12.70)	21 ft (6.40 m)	1 roll (cont.)	R4300
Fig. 33b	M21-750-461	B-461	Polyester	Black on White	0.750 (19.05)	21 ft (6.40 m)	1 roll (cont.)	R4300
<b>B-7425 Polypropylene</b>								
Fig. 33b	M21-375-7425	B-7425	Polypropylene	Black on White	0.375 (9.53)	21 ft (6.40 m)	1 roll (cont.)	R4300
Fig. 33b	M21-500-7425	B-7425	Polypropylene	Black on White	0.500 (12.70)	21 ft (6.40 m)	1 roll (cont.)	R4300
Fig. 33b	M21-750-7425	B-7425	Polypropylene	Black on White	0.750 (19.05)	21 ft (6.40 m)	1 roll (cont.)	R4300

## Water Dissolvable Paper Labels (B-403)

- B-403 completely dissolves in warm water within 30 seconds, leaving no adhesive residue.



Figure 33b



Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll	Ribbon in Cartridge
Fig. 33b	M21-750-403	B-403	Dissolvable Paper	Black on White	0.750 (19.05)	21 ft (6.40 m)	1 roll (cont.)	R4300