

Pre-Printed Wire Marker Cards

Self-Laminating Porta-Pack® Marker Books

- Use labeling pens or other markers to write on your legend
- Transparent part over-wraps provide snug fitting, self-laminating shield that resists oil, water and solvents
- For applications above or below ground

Catalog #	Legend	Marker Size Inch (mm)	Write-On Area Inch (mm)	Quantity of Each Legend
PWS-PK-14	Blank/Write-on	0.500 x 1.500 (12.70 x 38.00)	0.500 x 0.750 (12.70 x 19.00)	180
PWC-PK-1	Blank/Write-on	0.750 x 1.750 (19.00 x 44.40)	0.750 x 0.500 (19.00 x 12.70)	120
PWC-PK-3	Blank/Write-on	1.000 x 3.000 (25.40 x 76.20)	1.000 x 0.750 (25.40 x 19.00)	60
PWC-PK-6	Blank/Write-on	1.000 x 6.000 (25.40 x 152.40)	1.000 x 1.000 (25.40 x 25.40)	30
PWC-PK-36	Blank/Write-on	1.000 x 3.000 (25.40 x 76.20)	1.000 x 0.750 (25.40 x 19.00)	30
		1.000 x 6.000 (25.40 x 152.40)	1.000 x 1.000 (25.40 x 25.40)	15
Pre-Printed				
PWS-PK-1	0 to 9		-	45
PWS-PK-2	A thru Z, 0 thru 15, (+), (-), (/)		-	10
PWS-PK-3	1 to 45		-	10



Self-Laminating Wire Markers

BradySleeve™ Porta-Pack Marker Books

- Full-circle sleeve marker permits multiple-digit legend
- Includes permanent marking pen

Catalog #		Range of Wire Diameter Inch (mm)	Wire Gauge	Markers Per Book
B-319 Non-Shrink Polyolefin				
PCPS-0.4-2508-WT	Non-Shrink Polyolefin	0.030 - 0.100 (0.76 - 2.54)	16 to 20	630
PCPS-0.9-2508-WT	Non-Shrink Polyolefin	0.030 - 0.100 (0.76 - 2.54)	16 to 20	315
PCPS-0.4-3336-WT	Non-Shrink Polyolefin	0.090 - 0.150 (2.28 - 3.81)	12 to 16	420
PCPS-0.9-3336-WT	Non-Shrink Polyolefin	0.090 - 0.150 (2.28 - 3.81)	12 to 16	225
PCPS-0.4-3758-WT	Non-Shrink Polyolefin	0.125 - 0.175 (3.18 - 4.45)	10, 12	390
PCPS-0.9-3758-WT	Non-Shrink Polyolefin	0.125 - 0.175 (3.18 - 4.45)	10, 12	210
PCPS-0.4-5008-WT	Non-Shrink Polyolefin	0.160 - 0.250 (4.06 - 6.35)	8, 10	300
PCPS-0.9-5008-WT	Non-Shrink Polyolefin	0.160 - 0.250 (4.06 - 6.35)	8, 10	165
B-321 Heat-Shrink Polyolefin				
PHPCS-0.4-2508-WT	Heat-Shrink Polyolefin	0.035 - 0.075 (0.89 - 1.91)	16 to 20	630
PHPCS-0.9-2508-WT	Heat-Shrink Polyolefin	0.035 - 0.075 (0.89 - 1.91)	16 to 20	315
PHPCS-0.4-3336-WT	Heat-Shrink Polyolefin	0.075 - 0.130 (1.91 - 3.30)	12 to 16	420
PHPCS-0.9-3336-WT	Heat-Shrink Polyolefin	0.075 - 0.130 (1.91 - 3.30)	12 to 16	225
PHPCS-0.4-3758-WT	Heat-Shrink Polyolefin	0.130 - 0.160 (3.30 - 4.06)	10, 12	390
PHPCS-0.9-3758-WT	Heat-Shrink Polyolefin	0.130 - 0.160 (3.30 - 4.06)	10, 12	210
PHPCS-0.4-5008-WT	Heat-Shrink Polyolefin	0.160 - 0.235 (4.06 - 5.97)	8, 10	300
PHPCS-0.9-5008-WT	Heat-Shrink Polyolefin	0.160 - 0.235 (4.06 - 5.97)	8, 10	165



BradySleeve Wire Markers

Load Center And Residential Wire Markers

- Fits right on switch or circuit breaker
- Comes in ten page pocket-sized book for convenient use

Catalog #	Legend	Card Size Inch (mm)	Markers Per Card	Cards Per Pkg
PWM-LC-3	Assorted Load Center and Residential Legends	1.5" x 1.55"	45	10



Load Center and Residential Legends

Marking Pens

Catalog #		Qty.
MP-1	Black Fine Point	1 each
MP-2	Black Ultra Fine Point	1 each



Pre-Printed Labels

Wire Marker Cards