




1PL2/06, UV Rated Black, 1-Sided, 6-Port, #14-2/O AWG

By Burndy
Catalog # 1PL2/06



UV Rated Covering, Oxide inhibitor pre-installed, Same-Side, 6-Port Tap, #14-2/O AWG

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/O AWG
Conductor - AL Str Size Range	14 AWG - 2/O AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG

Conductor Size	• 2 AWG • 1 AWG • 1/0 • 2/O AWG
Conductor Type	14-2/O AWG • AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 2/O AWG

Configuration

Physical Attribute - Number of Screws	6
Number Of Ports	6
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	35.1 mm
Dimension - Height inch	1.38 in
Dimension - Height fraction	1.375 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	107 mm
Width	1.31 in
Dimension - Screw Size inch	7/16
Length	4.2 in
Dimension - Width mm	33 mm
Dimension - Width inch	1.31 in
Height	1.38 in
Dimension - Length Overall inch	4.20 in
Dimensions	4.2 in x 1.31 in x 1.38 in

Force Related

Installation Torque Recommended in-lb	120 in-lb
---------------------------------------	-----------

General

Insulation Type	Plastisol
-----------------	-----------

Trade Name	UNITAP™	Minimum Pack Quantity	10
Material - Hardware	Aluminum	Pallet Quantity	4500
Insulation	Y	Carton Quantity	100
Plated	N		
UPC	781810286876	Operational	
Hex Key	3/16	Temperature Rating	194° F
Material	Aluminum		
Plating Type	Unplated	Product Assets	
UPC 12 Digit	781810286876	Catalog [English]	
UPC 14 Digit GTIN	00781810286876	Catalog [English]	

Logistics

