

# IDXPERT™ Handheld Labeler

[www.BradyID.com/idxpert](http://www.BradyID.com/idxpert)

Portable Label Printers



**View Online!**

Visit [www.BradyID.com/idxpert](http://www.BradyID.com/idxpert) or scan this code for more information or to view a demo video of the IDXPERT Labeler.



## Your Complete Printing Solution:

IDXPERT cartridges with material and print ribbon .....Page 22

Brady's IDXPERT™ Handheld Labeler is the ideal tool for affordable, on-the-spot labeling in datacomm, electrical, and industrial workplaces. This 300 dpi thermal transfer label printing creates die-cut labels, self-laminating labels, sleeves and continuous tape labels.

## Three Versions Available:

1. "Qwerty" keyboard layout style for fast typing
2. "ABC" handheld style for maximum portability
3. "Continuous Only" version only prints on continuous lengths of material

| Catalog #       | Description                                                                 |
|-----------------|-----------------------------------------------------------------------------|
| XPERT-ABC       | Printer* - ABC Layout                                                       |
| XPERT-KEY       | Printer* - KEYBOARD Layout                                                  |
| XPERT-CONT      | Printer* - Continuous Printing Only                                         |
| XPERT-HC-ABC    | Hard Case for ABC Layout                                                    |
| XPERT-HC-KEY    | Hard Case for KEYBOARD Layout                                               |
| XPERT-AC        | AC Adapter                                                                  |
| LABXPRT-SER-USB | Serial-to-USB adapter for PC cable                                          |
| PCCABLE-1       | Spare PC Cable for Upgrades Only                                            |
| PCK-5           | Cleaning Kit                                                                |
| LM5STDE         | LabelMark™5 Software (single user)                                          |
| XPRT-ABC-KIT-LM | Printer* ABC Layout, AC Power Supply and LabelMark™5 Standard Software      |
| XPRT-KEY-KIT-LM | Printer* Keyboard Layout, AC Power Supply and LabelMark™5 Standard Software |

*\*Printer purchase included Hard Case, 1.5" Continuous Sample Roll Tape, PC cable, Product CD and 1 year Limited Warranty.*



## More Types of Labels

- Colored continuous tapes for lean, equipment and safety identification
- PermaSleeve® wire marker sleeves
- Self-laminating wire & cable markers
- Terminal block, patch panel, faceplate & outlet markers
- General-purpose industrial die-cut labels

## More Sizes

- Prints from .06" up to 1.25" characters on label stock up to 1.5" wide

## More Symbols

- Code 39 and 128 barcodes
- 82 symbols including electrical, voice/data, safety & protection, warning, and machine & operational

## More Brains

- Drop Lock & Go™ Smart Cartridges™ are fast to install and remove
- Electronically pre-calibrated to orient the label the way you need it with no special keys to press
- Print stand-alone or from a PC (with optional Brady LabelMark™ software)
- Memory to store frequently used set-ups

## Prints Clean & Fast

- Fast print speed, plus non-smearing thermal transfer print quality.
- Flexible text editing capabilities

## Less Waste

- Edge-to-edge printing on continuous tapes so you don't pay for unused label material
- Die-cut labels are pre-cut to the size you need


## Let the IDXPERT portable printer work for you.



Voice & Data Communications



PermaSleeve® Wire Marking Sleeves



Terminal Blocks



Self-Laminating Labels



Patch Panel & Faceplates



General ID  
...and many more!