




1PLMD25012, UV Black, Mount, 2-Side, 12-Port, #10 AWG-250

By Burndy
Catalog # 1PLMD25012

UV Rated Covering, Oxide inhibitor pre-installed, Mountable, 2-Sided, 12-Port Tap, #10 AWG-250 kcmil



Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes
Certification - UL Listed Direct Burial	No

Conductor

Conductor Size	10 AWG-250 KCMIL
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Str Size Range	10 AWG - 250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - AL Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG

- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil

Conductor - AL Str Size Range 10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	14
Connector Type	Multi Tap
Number Of Ports	12

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	2.64
Package Length	0.000 in
Dimension - Width mm	67 mm
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	331
Dimension - Height fraction	2-1/4 in
Dimension - Height inch	2.13
Package Height	0.000 in
Dimension - Height mm	56.6 mm
Length	13.03 in
Dimension - Length Overall inch	13.03
Width	2.64 in
Height	2.13 in
Dimensions	13.03 in x 2.64 in x 2.13 in

General

Material - Hardware	Aluminum
Insulation Type	Plastisol
Trade Name	UNITAP™
Plated	N
Insulation	Y
UPC 12 Digit	781810307571
UPC 14 Digit GTIN	00781810307571

Material

Hex Key

Plating Type

UPC

Aluminum

5/16

Unplated

781810307571

Operational

Temperature Rating

194° F

Product Assets

[Catalog \[English\]](#)

[Catalog \[English\]](#)

Logistics

Minimum Pack Quantity

1



A Hubbell brand