



1PLO42, UV Rated Black, Offset Entry, 2-Ports, #14-#4 AWG

By Burndy
Catalog # [1PLO42](#)

UV Rated Covering, Oxide inhibitor pre-installed, Opposite Side,
2-Port Tap, #14-4 AWG

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications


Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	14-4 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 4 AWG

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap



Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Dimension - Height fraction	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27 mm
Width	1.5 in
Dimension - Width fraction	1-1/2 in
Dimension - Screw Size inch	5/8
Length	1.08 in
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Height	1.25 in
Dimension - Length Overall inch	1.08 in
Dimensions	1.08 in x 1.5 in x 1.25 in

Force Related

Installation Torque	45 LBS/in
Recommended in-lb	

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
UPC	781810287521
Hex Key	1/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810287521
UPC 14 Digit GTIN	00781810287521

Logistics

Minimum Pack Quantity	1
Pallet Quantity	15000

Carton Quantity250

Product Assets

Operational

- Catalog [English]
- Catalog [English]

Temperature Rating194



A Hubbell brand