



AGSKIT250 Splice Kit, 1 AWG-250 kcmil, Al/Cu Rated

By Burndy
Catalog # [AGSKIT250](#)

Splice Kit, 1 AWG-250 kcmil, w/ Heavy Wall Heat Shrink Sleeve, Al/Cu Rated



Features

- Dual Rated - Aluminum or Copper/Aluminum Combinations
- Installed with common installation tools
- Heavy wall heat shrink sleeve is lined with adhesive material providing a positive seal against moisture egress

Application

For All Aluminum or Copper/Aluminum Combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	1 AWG-250 KCMIL
Conductor - Copper Solid Size	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	1 AWG-4/0 AWG
Conductor - AL Str Size	• 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	1 AWG-250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	1 AWG-250 kcmil
Conductor - Copper Str Size	• 1 AWG

- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil

Configuration

Connector Type	Splice/Heat Shrink Kit
----------------	------------------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in
Hex Size	5/16

General

Physical Attribute - Screw Type	Allen
Plated	N
Material - Hardware	Aluminum
Sub Brand	SPLICE KIT
UPC	781810175262
Type	AGSKIT, Above Grade
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810175262
UPC 14 Digit GTIN	00781810175262

Logistics

Pallet Quantity	630
Carton Quantity	10

Operational

Temperature Rating	194° F
--------------------	--------



A Hubbell brand