

BA14EL6, Vinyl Locking Fork Terminal, 16-14 AWG, #6 Stud

By Burndy
Catalog # [BA14EL6](#)

Vinyl Insulated Copper Locking Fork Terminal For 16 - 14 AWG, #6 Stud,
Bulk Packaged



Features

- Locking Fork Tongue design
- Allows for fast installation, screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking form is made from copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Dimensions

Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/50
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.29 in
Dimension - Hole Size inch	0.14 in
Dimension - Stud Size inch	#6
Dimension - Bolt Size fraction	#6
Length	0.87 in
Dimension - Z inch	0.23 in
Height	0.29 in
Dimension - Length Overall inch	0.87 in
Dimensions	0.87 in x 0.29 in x 0.29 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Physical Attribute - Tongue Type	Locking Fork
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810026915
Type	BA-EL, Locking
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026915
UPC 14 Digit GTIN	00781810026915

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)