



BDBMHC162/02, 2-Pole Power Distribution Block

By Burndy
Catalog # [BDBMHC162/02](#)

Aluminum Power Distribution Block, 2 Pole, Run: #14 - 2/0 AWG,
Tape: #14 - 2 AWG, 175 Amp/Pole

Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Run	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Number Of Poles	2
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Run	• 12 • 10 • 8 • 6 • 4 • 3 • 2 • 1

	• 1/0 • 2/0
Conductor - AL Str Tap Range	12-2
Conductor - AL Str Tap	• 12 • 10 • 8 • 6 • 4 • 3 • 2
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	14-2
Conductor - Copper Str Tap	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4 • 3 • 2

Current

Amperage Rating	175 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	82.6 mm
Length	3.57 in
Dimension - Height inch	3.25 in
Package Weight	0.000 lb.
Dimension - Width mm	91 mm
Dimension - Width inch	3.57 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Height	3.25 in
Width	3.88 in

Dimension - Length Overall	5.00 in
inch	
Dimensions	3.57 in x 3.88 in x 3.25 in

General

Plated	Y
Trade Name	VERSIPOLE™
UPC	781810645796
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810645796

UPC 14 Digit GTIN	00781810645796
-------------------	----------------

Logistics

Minimum Pack Quantity	1
Pallet Quantity	108
Carton Quantity	9

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand