



BA16E14, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # [BA16E14](#)

Vinyl Ring Terminal For 22 - 16 AWG



Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor - Copper Solid Size Range	20 AWG -22 AWG 16 AWG -18 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	20 AWG - 22 AWG 16 AWG - 18 AWG

Configuration

Physical Attribute - Number of Holes 1

Connector Type

Ring Terminal

Dimensions

Dimension - Pad Width inch	0.40 in
Package Height	0.000 in
Dimension - Hole Size fraction	10/37
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.41 in
Dimension - Hole Size inch	0.27 in
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Length	0.99 in
Dimension - Z inch	0.36 in
Height	0.41 in
Dimension - Length Overall inch	0.99 in
Dimensions	0.99 in x 0.41 in x 0.41 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Physical Attribute - Tongue Type	Ring
Sub Brand	VINYLUG
UPC	781810026717
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026717
UPC 14 Digit GTIN	00781810026717

Logistics

Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)



A Hubbell brand