



BA16E6, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy

Catalog # [BA16E6](#)

Vinyl Ring Terminal For 22 - 16 AWG



Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Industry Standard(s)	No
Buy America(n) Qualified	UL467
Certification - ETL	Contact Manufacturer
Standards - Industry Standards Met	No
Standards - RoHS Compliance	UL486
Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size Range	20 AWG -22 AWG 16 AWG -18 AWG
Conductor Size	22 - 16 AWG
Conductor - Copper Str Size Range	20 AWG - 22 AWG 16 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---



A Hubbell brand

Connector Type

Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Stud Size inch	#6
Width	0.26 in
Dimension - Z inch	0.18 in
Length	0.74 in
Dimension - Bolt Size fraction	#6
Dimension - Length Overall inch	0.74 in
Height	0.26 in
Dimensions	0.74 in x 0.26 in x 0.26 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	VINYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Shrouded
Type	Ring Tongue
UPC 12 Digit	781810026687
UPC 14 Digit GTIN	00781810026687
Material	Copper
Plating Type	Tin
UPC	781810026687

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)