



## BB024L9T14 Flexible Copper Braid, 9.00 in, Flexible copper braid jumpers designed to take up linear expansion and contraction

By Burndy

Catalog # [BB024L9T14](#)

Flexible Copper Braid, 9.00 in, Flexible copper braid jumpers designed to take up linear expansion and contraction

### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### Application

Flexible copper braid jumpers designed to take up linear expansion and contraction

### Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| EU RoHS Indicator                  | Yes |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |
| Certification - CSA Approved       | Yes |

### Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

### Current



|                           |    |
|---------------------------|----|
| Rating - Indoor Amperage  | 93 |
| Rating - Outdoor Amperage | 93 |

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 229 mm    |
| Dimension - Stud Size inch      | 1/4       |
| Length                          | 9 in      |
| Dimension - N inch              | 0.5 in    |
| Dimension - Length Overall inch | 9.00 in   |

### General

|                                       |                |
|---------------------------------------|----------------|
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 1              |
| Sub Brand                             | BRAID          |
| UPC                                   | 781810552537   |
| Type                                  | B              |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810552537   |
| UPC 14 Digit GTIN                     | 00781810552537 |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2250 |
| Carton Quantity       | 25   |

### Product Assets

[Catalog \[English\]](#)



A Hubbell brand