



BIBD2508, 2-Side, 8-Cond. Clear Ins.
MultiTap

By Burndy
Catalog # [BIBD2508](#)



#10 AWG - 250 kcmil, 8 Ports, Double-sided Entry, Al/Cu Rated,
Clear Plastisol allows visual confirmation conductor is properly
inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	8 AWG-250 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG

- 7 AWG
- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil

Conductor Size	10 AWG-250 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	8
Number Of Ports	8
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	54.1 mm
Dimension - Height inch	2.13 in
Dimension - Height fraction	2.125 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	195 mm
Dimension - Width fraction	2-16/25 in
Dimension - Width mm	67 mm
Dimension - Width inch	2.64 in
Dimension - Length Overall inch	7.66 in

General

Insulation Type	Plastisol
-----------------	-----------

Trade Name	UNITAP™	UPC 14 Digit GTIN	00781810224069
Material - Hardware	Aluminum	Logistics	
Insulation	Y		
Physical Attribute - Screw Type	Allen		
Plated	N	Pallet Quantity	768
Sub Brand	UNITAP	Carton Quantity	24
UPC	781810224069	Operational	
Type	BIBD, Multi-Port		
Hex Key	5/16	Temperature Rating	194
Material	Aluminum	Product Assets	
Plating Type	Unplated		
UPC 12 Digit	781810224069		
		Catalog [English]	
		Catalog [English]	



A Hubbell brand