



BIBD44, 2-Side, 4-Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD44](#)

#14 - 4 AWG, 4 Port, Double-sided Entry, Al/Cu Rated, Clear Plastisol
allows visual confirmation conductor is properly inserted



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 str
Conductor Size	14-4 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 4 AWG

Configuration

Physical Attribute - Number of Screws	4
Number Of Ports	4
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	31.8 mm
Dimension - Height inch	1.25 in
Dimension - Height fraction	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	50 mm
Dimension - Width fraction	1-1/2 in
Dimension - Screw Size inch	1/4
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Dimension - Length Overall inch	1.95 in

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	UNITAP
Product Type	Run/Tap
UPC	781810223864
Type	BIBD, Multi-Port
Hex Key	1/8
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810223864
UPC 14 Digit GTIN	00781810223864

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600

Carton Quantity	100	Product Assets
Operational		Catalog [English]
Temperature Rating	194	Catalog [English]
 A Hubbell brand		© 2026 Hubbell Incorporated. All rights reserved BRDY-BIBD44-SPEC-EN REV 7/2026